



**CAD/AEC/GIS • POS • HIGHER EDUCATION**

## **Epson SureColor T3760D / T5760D / T7760D/DL**

- Designed for high-speed, high-volume production with enhanced colour gamut
- Dual roll capability with auto loading and auto exchange
- Second roll can also be configured as an auto take-up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ XD3 ink for scratch and moisture resistant prints
- On-board high-speed PostScript for drag-n-drop printing
- Optional high-capacity SSD for efficient workgroup operation and rapid reprint
- Integrated pull-out media bin and Epson Cloud Solution PORT support
- Comprehensive warranty with on-site service up to 5 years (includes print head)<sup>1</sup>

# Epson SureColor T3760D / T5760D / T7760D/DL

Product Specifications	
<b>Print Specifications</b>	<b>Consumables</b>
Printhead	2.64" PrecisionCore™ TFP
Printing Resolution	2,400 x 1,200 dpi maximum
Ink Type	UltraChrome XD3 aqueous pigment ink
Colours	Photo Black, Matte Black, Cyan, Magenta, Yellow, Red
Ink Sizes	350 ml / 700 ml cartridges / 1.6 L pouches <sup>2</sup>
Nozzle Configuration	9600 nozzles (400 nozzles x 24 channels x 1 head)
Minimum Drop Size	3.5 pl
<b>Paper Handling</b>	
Loading	Single sheet and dual roll with autoloading (Second roll can optionally be configured as an auto take-up)
Roll Support	254 mm to 610 mm (T3760D) / 914 mm (T5760D) / 1,118 mm (T7760D/DL), 12.5 kg, 2/3" core <sup>3</sup> , 170 mm diameter max
Sheet Support	203 mm to 610 mm (T3760D) / 914 mm (T5760D) / 1,118 mm (T7760D/DL)
Paper Thickness	Cut-sheet: 0.07 mm to 0.8 mm Poster board: 0.8 mm to 1.5 mm Roll: 0.07 mm to 0.8 mm
<b>Operation</b>	
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct,
Memory	4 GB RAM + 960 GB optional SSD
Emulations	On-board High Speed Postscript, HPGL/2, HP-RTL <sup>4</sup>
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later
Product Features	Compact design with a flat top and illuminated platen All front loaded consumables Integrated pull-out media bin Direct front panel USB print support 4.3" colour touch screen control panel
Software Utilities	Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.
<b>Environmental</b>	
Physical	T3760D: 1,365 x 499 x 975 mm T5760D: 1,645 x 499 x 975 mm T7760D/DL: 1,848 x 499 x 975 mm
Energy Usage	
	T7760D 70 W Operating / 32 W Standby / 2 W Sleep
	T3760D, T7760DL 75 W Operating / 32 W Standby / 2 W Sleep
	T5760D 80 W Operating / 32 W Standby / 2 W Sleep
Acoustic Noise	Approx. 50 dB/A operating
	<b>Options</b>
	960GB SSD C12C936671
	Additional 24" Roll Feed Spindle C12C937711
	Additional 36" Roll Feed Spindle C12C937671
	Additional 44" Roll Feed Spindle C12C936171
	<b>Ordering Configurations</b>
	T3760D Printer with 1Yr Warranty <sup>1</sup> C11CH80401
	T5760D Printer with 1Yr Warranty <sup>1</sup> C11CH81401
	T7760D Printer with 1Yr Warranty <sup>1</sup> C11CH83401
	T7760DL Printer with 1Yr Warranty <sup>1</sup> C11CJ74401
	T3760D Printer with 3Yr CoverPlus <sup>1</sup> SCT3760D3YR
	T5760D Printer with 3Yr CoverPlus <sup>1</sup> SCT5760D3YR
	T7760D Printer with 3Yr CoverPlus <sup>1</sup> SCT7760D3YR
	T7760DL Printer with 3Yr CoverPlus <sup>1</sup> SCT7760DL3YR
	T3760D Printer with 5yr CoverPlus <sup>1</sup> SCT3760D5YR
	T5760D Printer with 5yr CoverPlus <sup>1</sup> SCT5760D5YR
	T7760D Printer with 5yr CoverPlus <sup>1</sup> SCT7760D5YR
	T7760DL Printer with 5Yr CoverPlus <sup>1</sup> SCT7760DL5YR
	<b>What's in the box</b>
	Printer, 2 x roll spindles, maintenance box/es, a set of 240 ml ink cartridges for T3760D/T5760D/T7760D, and 1.6 L ink pouches for T7760DL, AC power cable, setup guide, Environmental software (some requires web download &/or registration)



## Better Products for a Better Future

To find out more visit [www.epson.com.au/prographics/](http://www.epson.com.au/prographics/)

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations.

**IMPORTANT: This document contains pre-release data and specifications that are subject to change. Please refer to the websites listed below for latest information.**

**Epson Australia Pty Ltd**  
Level 1, 3 Talavera Road  
Macquarie Park NSW 2113  
Tel: 02 8899 3666  
[www.epson.com.au](http://www.epson.com.au)

**Epson New Zealand**  
Level 2, 9 Fanshawe Street  
Auckland 1010  
Tel: 09 366 6855  
[www.epson.co.nz](http://www.epson.co.nz)

**YOUR EPSON RESELLER**



For more information or detailed product specification, please call or visit us at  
**FUJIFILM Business Innovation Australia Pty Ltd**

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

V0.8 July 2023

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia  
Tel. +61 2 9856 5000 | [fujifilm.com/fbau](http://fujifilm.com/fbau)