



PRINT • COPY • SCAN • SHARE

## Epson SureColor T5760DM / T7760DM

- Designed for high-speed, high-volume production with enhanced colour gamut
- Integrated advanced scanner for scan and copy functionality
- Second roll can also be configured as an auto take-up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ XD3 ink for scratch and moisture resistant prints
- On-board high-speed PostScript for drag-n-drop printing
- High-capacity SSD included for efficient workgroup operation and rapid reprint
- Integrated pull-out media bin and Epson Cloud Solution PORT support
- Comprehensive warranty with on-site service up to 5 years (includes print head)<sup>1</sup>

# Epson SureColor T5760DM / T7760DM

| Product Specifications   |  |
|--|--|
| <b>Print Specifications</b>  |  |
| Printhead  | 2.64" PrecisionCore™ TFP   |
| Printing Resolution  | 2,400 x 1,200 dpi maximum  |
| Ink Type   | UltraChrome XD3 aqueous pigment ink  |
| Colours  | Photo Black, Matte Black, Cyan, Magenta, Yellow, Red   |
| Ink Sizes  | 350 ml / 700 ml cartridges   |
| Nozzle Configuration   | 9600 nozzles (400 nozzles x 24 channels x 1 head)  |
| Minimum Drop Size  | 3.5 pl   |
| <b>Paper Handling</b>  |  |
| Loading  | Single sheet and dual roll with autoloading (Second roll can optionally be configured as an auto take-up)  |
| Roll Support   | 254 mm to 914 mm (T5760DM) / 1,118 mm (T7760DM), 12.5 kg, 2/3" core <sup>2</sup> , 170 mm diameter max   |
| Sheet Support  | 203 mm to 914 mm (T5760DM) / 1,118 mm (T7760DM)  |
| Paper Thickness  | Cut-sheet: 0.07 mm to 0.8 mm<br>Poster board: 0.8 mm to 1.5 mm<br>Roll: 0.07 mm to 0.8 mm  |
| <b>Scanner Specifications</b>  |  |
| Technology   | Contact Image Sensor (CIS) with RGB filters  |
| Light Source   | Dual Light Source  |
| Resolution   | 600 dpi maximum  |
| <b>Scan &amp; Copy Support</b>   |  |
| Media Handling   | Single Sheet Front Loading   |
| Document Types   | Line & Text, Blueprint & Blueprint inverted, Tracing Paper & Poster  |
| Scan To Formats  | JPEG, PDF, Encrypted PDF, PDF/A, TIFF  |
| Copy Function  | 1-99 Sheets, 25-755% scaling, Auto Fit   |
| Max copy length  | 5.494 m (300 dpi)  |
| <b>Operation</b>   |  |
| Connectivity   | USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct   |
| Memory   | 4 GB RAM + 960 GB SSD  |
| Emulations   | On-board High Speed Postscript, HPGL/2, HP-RTL <sup>3</sup>  |
| OS Compatibility   | Windows 11/10/8.1/8/7/Vista/XP (32bit/64bit)<br>MacOS 10.6.8 or later  |
| Product Features   | Compact design with a flat top and illuminated platen<br>Advanced Integrated dual light scanner<br>All front loaded consumables<br>Integrated pull-out media bin<br>Direct front panel USB print support<br>4.3" colour touch screen control panel |
| Software Utilities   | Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.   |
| <b>Environmental</b>   |  |
| Physical   | T5760DM: 1,645 x 499 x 975 mm<br>T7760DM: 1,848 x 499 x 975 mm   |
| Energy Usage   | 90 W Operating / 44 W Standby / 2 W Sleep  |
| Acoustic Noise   | Approx. 50 dB/A operating  |
| <b>Consumables</b>   |  |
| T5760DM / T7760DM  |  |
| UltraChrome™ XD3 350 ml Ink Carts  | C13T50U100~F00   |
| UltraChrome™ XD3 700 ml Ink Carts  | C13T50M100~F00   |
| Replacement Maintenance Box  | C13S210115   |
| Replacement Auto Cutter Blade  | C13S210117   |
| Replacement Borderless Maintenance Box   | C13S210116   |
| <b>Options</b>   |  |
| Additional 36" Roll Feed Spindle   | C12C937671   |
| Additional 44" Roll Feed Spindle   | C12C936171   |
| <b>Ordering Configurations</b>   |  |
| T5760DM Printer with 1Yr Warranty <sup>1</sup>   | C11CH82401   |
| T5760DM Printer with 3Yr Warranty <sup>1</sup>   | SCT5760DM3YR   |
| T5760DM Printer with 5Yr Warranty <sup>1</sup>   | SCT5760DM5YR   |
| T7760DM Printer with 1Yr Warranty <sup>1</sup>   | C11CH84401   |
| T7760DM Printer with 3Yr Warranty <sup>1</sup>   | SCT7760DM3YR   |
| T7760DM Printer with 5Yr Warranty <sup>1</sup>   | SCT7760DM5YR   |
| <b>What's in the box</b>   |  |
| Printer, 2 x roll spindles, maintenance box/es, a set of 240 ml ink cartridges, AC power cable, setup guide, software (some requires web download &/or registration) |  |

<sup>1</sup> CoverPlus on these models is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus including the associated terms and conditions.  
<sup>2</sup> 3" core for plain paper rolls only.  
<sup>3</sup> HP-GL/2 and HP-RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP-RTL (CMYK type not supported for the latter) language data accurately depending on your system environment or type of print data use. Please ensure you run printing tests prior to purchase if these functions are essential. Contact your local Epson representative or Epson authorised reseller to arrange testing.



To find out more visit [www.epson.com.au/prographics/](http://www.epson.com.au/prographics/)

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations.

**Epson Australia Pty Ltd**  
Level 1, 3 Talavera Road  
Macquarie Park NSW 2113  
Tel: 02 8899 3666  
[www.epson.com.au](http://www.epson.com.au)

**Epson New Zealand**  
Level 2, 9 Fanshawe Street  
Auckland 1010  
Tel: 09 366 6855  
[www.epson.co.nz](http://www.epson.co.nz)

VO.2 June 2023

ABN: 91 002 625 783

YOUR EPSON RESELLER