



PRINT • COPY • SCAN • SHARE

## Epson SureColor T5760DM / T7760DM

- Designed for high-speed, high-volume production with enhanced colour gamut
- Integrated advanced scanner for scan and copy functionality
- Second roll can also be configured as an auto take-up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ XD3 ink for scratch and moisture resistant prints
- On-board high-speed PostScript for drag-n-drop printing
- High-capacity SSD included for efficient workgroup operation and rapid reprint
- Integrated pull-out media bin and Epson Cloud Solution PORT support
- Comprehensive warranty with on-site service up to 5 years (includes print head)<sup>1</sup>

# Epson SureColor T5760DM / T7760DM

## Product Specifications

Print Specifications		Software Utilities	Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.
Printhead	2.64" PrecisionCore™ TFP		
Printing Resolution	2,400 x 1,200 dpi maximum		
Ink Type	UltraChrome XD3 aqueous pigment ink		
Colours	Photo Black, Matte Black, Cyan, Magenta, Yellow, Red		
Ink Sizes	350 ml / 700 ml cartridges		
Nozzle Configuration	9600 nozzles (400 nozzles x 24 channels x 1 head)		
Minimum Drop Size	3.5 pl		
Paper Handling		Environmental	
Loading	Single sheet and dual roll with autoloading (Second roll can optionally be configured as an auto take-up)	Physical	T5760DM: 1,645 x 499 x 975 mm T7760DM: 1,848 x 499 x 975 mm
Roll Support	254 mm to 914 mm (T5760DM) / 1,118 mm (T7760DM), 12.5 kg, 2/3" core <sup>2</sup> , 170 mm diameter max	Energy Usage	90 W Operating / 44 W Standby / 2 W Sleep
Sheet Support	203 mm to 914 mm (T5760DM) / 1,118 mm (T7760DM)	Acoustic Noise	Approx. 50 dB/A operating
Paper Thickness	Cut-sheet: 0.07 mm to 0.8 mm Poster board: 0.8 mm to 1.5 mm Roll: 0.07 mm to 0.8 mm	Consumables	
Scanner Specifications		T5760DM / T7760DM	
Technology	Contact Image Sensor (CIS) with RGB filters	UltraChrome™ XD3 350 ml Ink Carts	C13T50U100~F00
Light Source	Dual Light Source	UltraChrome™ XD3 700 ml Ink Carts	C13T50M100~F00
Resolution	600 dpi maximum	Replacement Maintenance Box	C13S210115
Scan & Copy Support		Replacement Auto Cutter Blade	C13S210117
Media Handling	Single Sheet Front Loading	Replacement Borderless Maintenance Box	C13S210116
Document Types	Line & Text, Blueprint & Blueprint inverted, Tracing Paper & Poster	Options	
Scan To Formats	JPEG, PDF, Encrypted PDF, PDF/A, TIFF	Additional 36" Roll Feed Spindle	C12C937671
Copy Function	1-99 Sheets, 25-755% scaling, Auto Fit	Additional 44" Roll Feed Spindle	C12C936171
Max copy length	5.494 m (300 dpi)	Ordering Configurations	
Operation		T5760DM Printer with 1Yr Warranty <sup>1</sup>	C11CH82401
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct	T5760DM Printer with 3Yr Warranty <sup>1</sup>	SCT5760DM3YR
Memory	4 GB RAM in HW + 4 GB RAM in Adobe PostScript unit + 960 GB SSD	T5760DM Printer with 5Yr Warranty <sup>1</sup>	SCT5760DM5YRR
Emulations	On-board High Speed Postscript, HPGL/2, HP-RTL <sup>3</sup>	T7760DM Printer with 1Yr Warranty <sup>1</sup>	C11CH84401
OS Compatibility	Windows 11/10/8.1/8/7/Vista/XP (32bit/64bit) MacOS 10.6.8 or later	T7760DM Printer with 3Yr Warranty <sup>1</sup>	SCT7760DM3YR
Product Features	Compact design with a flat top and illuminated platen Advanced Integrated dual light scanner All front loaded consumables Integrated pull-out media bin Direct front panel USB print support 4.3" colour touch screen control panel	T7760DM Printer with 5Yr Warranty <sup>1</sup>	SCT7760DM5YRR
		What's in the box	
		Printer, 2 x roll spindles, maintenance box/es, a set of 240 ml ink cartridges, AC power cable, setup guide, software (some requires web download &/or registration)	

<sup>1</sup> CoverPlus on these models is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus including the associated terms and conditions.

<sup>2</sup> 3" core for plain paper rolls only.

<sup>3</sup> HP-GL/2 and HP-RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP-RTL (GMYK type not supported for the latter) language data accurately depending on your system environment or type of print data use. Please ensure you run printing tests prior to purchase if these functions are essential. Contact your local Epson representative or Epson authorised reseller to arrange testing.



To find out more visit [www.epson.com.au/prographics/](http://www.epson.com.au/prographics/)

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations.

**Epson Australia Pty Ltd**  
Level 1, 3 Talavera Road  
Macquarie Park NSW 2113  
Tel: 02 8899 3666  
[www.epson.com.au](http://www.epson.com.au)

**Epson New Zealand**  
Level 2, 9 Fanshawe Street  
Auckland 1010  
Tel: 09 366 6855  
[www.epson.co.nz](http://www.epson.co.nz)

VO.3 August 2023

ABN: 91 002 625 783

### YOUR EPSON RESELLER



For more information or detailed product specification, please call or visit us at  
**FUJIFILM Business Innovation Australia Pty Ltd**

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

Level 4, 54 Waterloo Road, Macquarie Park NSW 2113  
Contact us at [fujifilm.com/fbau](http://fujifilm.com/fbau) or 13 14 12