



**Photo Retail • Print Service Provision**

## Epson SureColor P6560D (24") / P8560D/DL (44")

- Designed for high-speed, high-volume production with enhanced gradation
- Dual roll capability with auto loading and auto exchange
- Second roll can also be configured as an auto take-up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ PRO6 ink for scratch and moisture resistant prints
- On-board high-speed PostScript for drag-n-drop printing
- Optional high-capacity SSD for efficient workgroup operation and rapid reprints
- Integrated pull-out media bin and Epson Cloud Solution PORT support
- Comprehensive warranty with on-site service up to 5 years (includes print head)<sup>1</sup>

# Epson SureColor P6560D (24") / P8560D/DL (44")

## Product Specifications

Print Specifications	
Print Head	2.64" PrecisionCore™ TFP
Printing Resolution	2,400 x 1,200 dpi maximum
Ink Type	UltraChrome PRO6 aqueous pigment ink
Colours	Photo Black, Matte Black, Cyan, Magenta, Yellow, Gray
Ink Sizes	350 ml / 700 ml cartridges / 1.6 L pouches <sup>2</sup>
Nozzle Configuration	9600 nozzles (400 nozzles x 24 channels x 1 head)
Minimum Drop Size	3.5 pl
Paper Handling	
Loading	Single sheet and dual roll with autoloading (Second roll can optionally be configured as an auto take-up)
Roll Support	254 mm to 610 mm (P6560D) / 1,118 mm (P8560D/DL), 12.5 kg, 2/3" core <sup>3</sup> , 170 mm max diameter
Sheet Support	203 mm to 610 mm (P6560D) / 1,118 mm (P8560D/DL)
Paper Thickness	Cut-sheet: 0.07 mm to 0.8 mm Poster board: 0.8 mm to 1.5 mm Roll: 0.07 mm to 0.8 mm
Operation	
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct
Memory	RAM + 960 GB optional SSD
Emulations	On-board High Speed Postscript, HPGL/2, HP-RTL <sup>4</sup>
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later
Product Features	
	Compact design with a flat top and illuminated platen All front loaded consumables Integrated pull-out media bin Direct front panel USB print support 4.3" colour touch screen control panel
Software Utilities	
	Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.
Environmental	
Physical	P6560D: 1,365 x 499 x 975 mm P8560D/DL: 1,848 x 499 x 975 mm
Energy Usage	
	<b>P8560D:</b> 70 W Operating / 32 W Standby / 2 W Sleep
	<b>P6560D, P8560DL:</b> 75 W Operating / 32 W Standby / 2 W Sleep
Acoustic Noise	Approx. 50 dB/A operating

Consumables	
<b>P6560D / P8560D</b>	
UltraChrome™ PRO6 350 ml Ink Carts	C13T48U100~E00
UltraChrome™ PRO6 700 ml Ink Carts	C13T48M100~E00
<b>P8560DL</b>	
UltraChrome™ PRO6 1.6 L Ink Pouches	C13T53F100~800
Replacement Maintenance Box	C13S210115
Replacement Auto Cutter Blade	C13S210117
Replacement Borderless Maintenance Box	C13S210116
Options	
960GB SSD	C12C936671
Additional 24" Roll Feed Spindle	C12C937711
Additional 36" Roll Feed Spindle	C12C937671
Additional 44" Roll Feed Spindle	C12C936171
Ordering Configurations	
P6560D Printer with 1Yr Warranty <sup>1</sup>	C11CJ49401
P6560D Printer with 3Yr CoverPlus <sup>1</sup>	SCP6560D3YR
P6560D Printer with 5Yr Warranty <sup>1</sup>	SCP6560D5YR
P8560D Printer with 1Yr Warranty <sup>1</sup>	C11CJ50401
P8560D Printer with 3Yr CoverPlus <sup>1</sup>	SCP8560D3YR
P8560D Printer with 5Yr CoverPlus <sup>1</sup>	SCP8560D5YR
P8560DL Printer with 1Yr Warranty <sup>1</sup>	C11CJ75401
P8560DL Printer with 3Yr CoverPlus <sup>1</sup>	SCP8560DL3YR
P8560DL Printer with 5Yr CoverPlus <sup>1</sup>	SCP8560DL5YR

**What's in the box**  
Printer, 2 x roll spindles, maintenance box/es, a set of 240 ml ink cartridges for P6560D/P8560D, and 1.6 L ink pouches for P8560DL, AC power cable, setup guide, software (some requires web download &/or registration)

<sup>1</sup> CoverPlus on these models is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus including the associated terms and conditions.

<sup>2</sup> 1.6 L ink pouches are for model P8560DL only.

<sup>3</sup> 3" core for plain paper rolls only.

<sup>4</sup> HP-GL/2 and HP-RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP-RTL (CMYK type not supported for the latter) language data accurately depending on your system environment or type of print data use. Please ensure you run printing tests prior to purchase if these functions are essential. Contact your local Epson representative or Epson authorised reseller to arrange testing.



PRECISIONCORE

Epson CoverPlus

Fast. Reliable. Professional



To find out more visit [www.epson.com.au/prographics/](http://www.epson.com.au/prographics/)

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations.

**IMPORTANT: This document contains pre-release data and specifications that are subject to change. Please refer to the websites listed below for latest information.**

Epson Australia Pty Ltd  
Level 1, 3 Talavera Road  
Macquarie Park NSW 2113  
Tel: 02 8899 3666  
[www.epson.com.au](http://www.epson.com.au)

Epson New Zealand  
Level 2, 9 Fanshawe Street  
Auckland 1010  
Tel: 09 366 6855  
[www.epson.co.nz](http://www.epson.co.nz)

VO.9 June 2023

ABN: 91 002 625 783

YOUR EPSON RESELLER

**EPSON**

**FUJIFILM**

For more information or detailed product specification, please call or visit us at  
**FUJIFILM Business Innovation Australia Pty Ltd**

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

Level 4, 54 Waterloo Road, Macquarie Park NSW 2113  
Contact us at [fujifilm.com/fbau](http://fujifilm.com/fbau) or 13 14 12