



SureColor R5000/5000L

- Produce durable signs and banners, POS and POP, wallpaper¹ and decor, wall and floor decals with consistent sizing and superior colour
- Reduced curing temperature for enhanced media compatibility
- Accurate and consistent imaging enables output to suit premium tiling
- Ink cures quickly for immediate job turnaround with high scratch resistance
- Efficient roll-to-roll production with bulk ink CISS and integrated auto take-up (ATU)
- Enhanced reliability with reduced maintenance and running costs
- Ships complete with easy-to-use Epson Edge Print software
- Service cover extendable up to 5 years with optional user-replaceable printheads²
- Epson Cloud Solution PORT for enhanced management and support

SureColor R5000/5000L

Product Specifications

PRINT SYSTEM	
Print Engine	Self-cleaning 2.6" PrecisionCore Micro TFP printhead with ink-less nozzle status monitoring & compensation, Variable Sized Dot Technology (VSdT), Precision Dot Technology, integrated crash guards and sensor, optional user-replaceable printheads ²
Media Handling	Downloadable print profiles, auto skew correction, advanced media tracking with auto skew correction, integrated auto take-up (ATU), multi-stage & multi-element heater with independent temp adjustment 1200 x 2400 dpi (max res), 4.9 pl min drop size
Print Quality	
INK SYSTEM	
Type	Epson UltraChrome RS (Resin/Latex)
Colour Set	R5000: 6-colour + optimiser & maintenance liquid R5000L: 2 x 6-colour + optimiser & maintenance liquid
Ink Size	1.5 L pouch
PRODUCTION SPEEDS ³	
Banner & wallpaper	21 m ² /h, 600 x 1200 dpi, 6 pass
Vinyl & Paper	15.1 m ² /h, 1200 x 1200 dpi, 9 pass
Film	5.2 m ² /h, 1200 x 2400 dpi, 26 pass
MEDIA SUPPORT	
Sizing	300-1626 mm (64") wide, 1 mm max thickness
Input	Single roll, 45 kg max weight, 250 mm max diameter
Output	Sheet (manual cut) or roll (200 mm max diameter)
Min Margins	5 mm each side (10 mm with edge plates)
MANAGEMENT	
Features	See-through platen cover with integrated lighting, 4.3" colour touch control panel, remote email status and error reporting
Included Software	Epson Edge Print, Edge Dashboard, Accounting Tool & Cloud Solution PORT service
PHYSICAL	
Dimensions (W x D x H)	2949 x 1045 x 1605 mm
Weight (excluding ink)	R5000: 427 kg / R5000L: 447 kg

INTEGRATION	
Recommended Space (W x D x H)	2.95 x 1.1 x 1.8 m
Operational Temp	15 to 30°C (20 to 25°C recommended)
Operational Humidity	20 to 80% (40 to 60% recommended)
Power Requirement	16 A 240 V 50/60 Hz
Power Consumption	4.6 kW operating/ 220 W ready/ 46 W sleep
Operational Noise	66.1 dB
Connectivity	USB2.0, 100BASE-TX/1000BASE-T
OPTIONS	
YR2SCR5000	Year 2 onsite CoverPlus
YR3SCR5000	Year 3 onsite CoverPlus
YR4SCR5000	Year 4 onsite CoverPlus
YR5SCR5000	Year 5 onsite CoverPlus
YR2SCR5000L	Year 2 onsite CoverPlus
YR3SCR5000L	Year 3 onsite CoverPlus
YR4SCR5000L	Year 4 onsite CoverPlus
YR5SCR5000L	Year 5 onsite CoverPlus
CONSUMABLES ⁴	
C13S210100	Replacement head wiper
C13S210103	Cleaning kit
C13T45X100	1 x 1.5 L cleaning liquid pouch (R5000 & R5000L)
C13T48F100~F600	1 x 1.5 L KCMYLcLm ink pouch (R5000)
C13T45U700	1 x 1.5 L optimiser pouch (R5000)
C13T45U800	1 x 1.5 L maintenance liquid (R5000)
C13T45U100~U600	2 x 1.5 L KCMYLcLm ink pouch (R5000L)
C13T45U700	2 x 1.5 L optimiser pouch (R5000L)
C13T45U800	2 x 1.5 L maintenance liquid (R5000L)
CONFIGURATION OPTIONS ⁵	
SCR50001YR	Printer with 1-year onsite warranty
SCR50003YR	Printer with 1-year onsite warranty + 2-year CoverPlus
SCR50005YR	Printer with 1-year onsite warranty + 4-year CoverPlus
SCR5000L1YR	Printer with 1-year onsite warranty
SCR5000L3YR	Printer with 1-year onsite warranty + 2-year CoverPlus
SCR5000L3YR	Printer with 1-year onsite warranty + 4-year CoverPlus



R5000: 12 L CISS
R5000L: 2 x 12 L with auto hot-swap



Advanced self-cleaning, precision temperature and air flow control



Advanced media tracking and tension control

Epson CoverPlus

Fast. Reliable. Professional.

Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and are trademarks of their respective owners; Epson disclaims any and all rights. Specifications are subject to change without notice. Visit www.epson.com.au or www.epson.co.nz for the latest information.

Epson Australia Pty Ltd
www.epson.com.au

Epson New Zealand
www.epson.co.nz

07/2025

ABN: 91 002 625 783

EPSON

FUJIFILM

For more information or detailed product specification, please call or visit us at
FUJIFILM Business Innovation Australia Pty Ltd

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

Level 4, 54 Waterloo Road, Macquarie Park NSW 2113
Contact us at fujifilm.com/fbau or 13 14 12