



PRINT • SCAN • COPY • SHARE

Epson SureColor T5460M (36")

- Designed for CAD, GIS, POS, posters and educational applications
- Integrated large format print, scan, and copy functionality
- Prints an A1 print in as little as 22s on cut-sheet and roll media
- Economical operation with low power consumption and cost-effective ink cartridges in a choice of 350ml and 110ml capacity
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment Ultrachrome™ XD2 ink for scratch and moisture resistant prints with super fine lines and solid fills
- High speed mono and colour scanning with support for highlighter mark-up
- Comprehensive warranty with comprehensive on-site service cover extendable up to 5 years (including the printhead)*1

Epson SureColor T5460M

Product Specifications

Print Specifications		UltraChrome™ XD2 Aqueous Pigment Inks	
Printhead	PrecisionCore™ TFP	110 ml Cartridges	
Printing Resolution	2,400 x 1,200 dpi maximum	UltraChrome™ XD2 Black	C13T41V500
Nozzle Configuration	800 nozzles per colour	UltraChrome™ XD2 Cyan	C13T41V200
Variable Drop Size	Yes, 4.0 pl minimum	UltraChrome™ XD2 Magenta	C13T41V300
Ink Type	UltraChrome XD2 aqueous pigment ink	UltraChrome™ XD2 Yellow	C13T41V400
Colours	Magenta, Yellow, Cyan, Black	350 ml Cartridges	
Ink Cartridge Sizes	110 ml/350 ml (supports mixed size cartridges)	UltraChrome™ XD2 Black	C13T41M500
Printing Speed	22 secs / A1 on plain paper	UltraChrome™ XD2 Cyan	C13T41M200
Scan Speed	19.05 cm/sec (7.5 ips) mono (200 dpi) ²	UltraChrome™ XD2 Magenta	C13T41M300
	11.43 cm/sec (4.5 ips) colour (200 dpi) ²	UltraChrome™ XD2 Yellow	C13T41M400
Copy Speed	44 sec colour/	Options	
	38 sec mono per A1 sheet at 200 dpi ²	Maintenance Box	C13T699700
Paper Handling	Single roll: 329 mm to 914 mm (36") 0.08~0.3 mm thick) 2/3" core ³ , max 150/170 mm diameter max roll weight 12 kg	Auto Cutter Blade	C13S902007
		Borderless Pad Kit	C13S400064
Roll based	A4 to A0 0.08~0.3 mm thick	Scanner Cleaning Kit	B12B819291
		A0 Document Carrier Sheet	C12C936461
Sheet based	A4 to A0 0.08~0.3 mm thick	Roll Feed Spindle 36"	C12C933301
		Ordering Configurations	
Scan Engine	CIS with RGB filters Dual Light Source	T5460M with 1 Year Warranty	C11CH65401
Scan Support	Single sheet A4 to A0, 0.8 mm max thick	T5460M with 3 Year CoverPlus	SCT5460M3YR
Connectivity	USB 3.0, 1000/100 base-T, WiFi, WiFi direct, AirPrint	T5460M Printer with 1Yr Wty + 2 x 2Yr CoverPlus	SCT5460M5YR
Memory	1 GB RAM + 8 GB Flash Memory	What's in the box	
Emulations	HPGL/2, HP-RTL ⁴	Printer, printer stand and basket, a set of 110 ml ink cartridges, AC power cable, setup guide, software CD, maintenance box	
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later	¹ Additional charges may apply for on-site service in non-metro areas and warranty cover may be limited if equipment is not operated and maintained appropriately. For terms and conditions on Epson Australia and New Zealand service and warranty cover please refer to the relevant web sites.	
Product Features	Direct USB printing ⁵ Scan to Tiff/Jpeg/PDF, adjustable copy scaling	² This is the actual scan/copy time. Product specifications are subject to change without notice.	
Software	Print Driver, LFP Print Plug-In for MS Office, LFP Account Tool, Epson Edge Dashboard	³ 3" core for plain paper rolls only	
Physical	1,385 x 750 x 1,070 (WxDxH)	⁴ HP-GL/2 and HP RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP RTL language data accurately depending on your system environment or type of print data use. In order to ensure correct printing results, please make sure that you run a printing test prior to deciding on purchasing the printer. Ask your local Epson representative or Epson authorised reseller for your test.	
Energy Usage	34 W operating/13 W Standby/1.3 W Sleep	⁵ For details please visit the relevant Epson websites	
Acoustic Noise Level	Approx. 50 dB (operating)	For further information please contact Epson Australia Pty Limited ABN 91 002 625 783 or visit www.epson.com.au . Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.	



Epson CoverPlus

Fast. Reliable. Professional



PRECISIONCORE

The integrated high-resolution scanner supports documents up to A0 with scan to USB, scan to file, scan to email, and direct copy (with adjustable scaling).

To find out more visit www.epson.com.au/prographics/

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. PANTONE® is the property of Pantone LLC. All other names and logos herein are for identification purpose only and are trademarks of their respective owners; Epson disclaims any and all rights. All print samples shown herein are simulations.

Epson Australia Pty Ltd
www.epson.com.au

Epson New Zealand
www.epson.co.nz

VO.5 February 2025

ABN: 91 002 625 783

EPSON

FUJIFILM

For more information or detailed product specification, please call or visit us at
FUJIFILM Business Innovation Australia Pty Ltd

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

Level 4, 54 Waterloo Road, Macquarie Park NSW 2113
Contact us at fujifilm.com/fbau or 13 14 12