

## Operating Environment of Print Utility

Item	Description
<b>Network Protocol</b>	LPD
<b>&lt;iOS&gt; Supported Models / Supported Operating System</b>	iPad (7th generation) or later, iPad Air (3rd generation) or later, iPad Pro (2018 models or later), iPad mini 5 or later, iPhone XS / XR or later iOS 18.0 or later *1, iPad OS 18.0 *1
<b>&lt;Android&gt; Tested devices &amp; OS versions</b>	Google Pixel6a (Android™15.0) Google Pixel7a (Android™14.0) Google Pixel7 (Android™13.0) Google Pixel5 (Android™12.0) Google Pixel4 (Android™11.0) Lenovo Yoga Tab 11 (Android™12.0) Sony Xperia 5 (Android™ 10.0) Sony Xperia XZ3 (Android™ 9.0) Samsung Galaxy S10 (Android™ 10.0) Samsung Galaxy S8 (Android™ 9.0) Samsung Galaxy Tab S5e (Android™ 9.0) Vivo iQoo (Android™ 9.0)
<b>Supported Languages</b>	English, Chinese (Simplified / Traditional), Korean, Japanese, Thai, Vietnamese, Indonesian
<b>Features*2</b>	Print <ul style="list-style-type: none"> <li>- Printing photos saved in the photo album</li> <li>- Printing photos taken by the internal camera</li> <li>- Printing DocuWorks and PDF documents Printing from Application</li> <li>- Server-less On-Demand Print</li> <li>- Working with ApeosWare Management Suite 2</li> <li>- Working with FUJIFILM IWPro</li> </ul> Scan to Mobile Capture Copy E-mail Scan to Folder Fax Favorites Linking with NFC

<b>Print</b>	<b>Printing photo/image/website</b>	<p>Specify the number of copies (max 99)</p> <p>Paper size: A3, A4, Letter, A5, B4, B5, 4 x 6" (101.6 x 152.4 mm), 8.5x 14", 11 x 17", 2L-size (127 x 178 mm), Postcard (100 x 148 mm)</p> <p>Image orientation: Portrait / Landscape</p> <p>Output Colour: On / Off</p> <p>2-sided print: On / Off</p> <p>Pages Per Sheet: 2 Pages Up / 4 Pages Up / 8 Pages Up / 16 Pages Up / 32 Pages Up (32 Pages up only for printing from photo gallery)</p> <p>Stapling: Off / 1 Staple Top Left</p> <p>Paper tray: Automatically Select / Bypass tray</p> <p>Paper type: Plain / Heavy weight / Heavy weight Reload</p> <p>Authentication and Accounting</p>
	<b>For PDF/ DocuWorks documents</b>	<p>Specify the number of copies (max 99)</p> <p>Paper size: Same as Paper Size, A4, A3, A5, B4, B5, Letter, Legal</p> <p>Collated: On / Off</p> <p>Output Colour: On / Off</p> <p>2-sided print: 1sided Print / 2sided Print / 2sided, Flip on short Edge</p> <p>Pages Per Sheet: 2 Pages Up / 4 Pages Up</p> <p>Stapling: Off / 1 Staple Top Left</p> <p>Hole Punch: No hole punch, 2-hole punch, 3-hole punch, 4-hole punch</p> <p>Paper tray: Automatically Select / Bypass tray</p> <p>Authentication and Accounting</p>
<b>Scan to Mobile*<sup>2</sup></b>		File Format (JPEG / PDF / DocuWorks), Scan Method, Image Type (Full Colour / Grayscale), Scan Size (A4 / Letter), Resolution (200 dpi / 300 dpi)
<b>Copy*<sup>2</sup></b>		Quantity, Output Colour, Original Size, 2 Sided, Paper Supply, Reduce / Enlarge, Paper per Side, Lighten / Darken, Staple, Original Type, Original Orientation, Background Suppression, Negative Image
<b>Fax*<sup>2</sup></b>		Resolution, Original Size, 2 Sided, Lighten / Darken, Original Type You can select the recipient e-mail address from the phonebook of your smartphone or tablet.
<b>E-mail*<sup>2</sup></b>		File Format (PDF, XDW, TIFF/JPEG Auto, TIFF), Colour Scanning, Original Size, 2 Sided, Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression You can select the recipient e-mail address from the phonebook of your smartphone or tablet. Only one e-mail address can be specified as a recipient.
<b>Scan to Folder*<sup>2</sup></b>		Colour Scanning, Original Size, 2 Sided, Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression.
<b>Operability</b>		Text to Speech, Colour inversion, Enlarged screen display, Gesture UI, External keyboard can be connected
<b>Supported authentication methods</b>		Non-authentication (including Deemed authentication) Local authentication (including Server-less Authentication Kit)

\*1: Use of the latest version is recommended.

\*2: These functions may not be available depending on the type of MFP.