

Remanufactured machines
A3 Colour Multifunction Printer

ApeosPort C5570 R / C3570 R

Functions & Specifications

Basic Specifications/Copy Function

Item	Description		
	C5570 R	C3570 R	
Type	Console		
Memory capacity	4 GB (Max: 4 GB)		
Storage Device Capacity ^{*1}	128 GB		
Colour Capability	Full colour		
Scan Resolution	600 x 600 dpi		
Printing Resolution	1,200 x 2,400 dpi (High Resolution photo), 600 x 600 dpi (Text / Text-Photo / Photo / Map)		
Warm-up Time ^{*2}	[Embedded Plug-ins / Custom Services] ^{*3} When enabled: 30 seconds or less (23 degrees Celsius room temperature) When disabled: 24 seconds or less (23 degrees Celsius room temperature)		
Recovery Time ^{*4} (Recovery Time from Sleep mode)	11 seconds or less (23 degrees Celsius room temperature)	4 seconds or less (23 degrees Celsius room temperature)	
Original Size	Maximum of A3, 11 x 17", 297 x 432 mm for both Sheet and Book		
Paper Size	Max	SRA3 (320 x 450 mm), 12 x 18" (305 x 457 mm), A3 [12 x 19" (305 x 483 mm), 320 x 483 mm when using Bypass Tray]	
	Min	A5, Postcard (100 x 148 mm) [89 x 98 mm when using Bypass Tray]	
	Image loss width ^{*5}	Lead edge 4.0 mm, Trail edge 2.0 mm, Right/Left edge 2.0 mm	
Paper Weight ^{*6}	Paper Tray	52 to 300 gsm	
	Bypass Tray	52 to 300 gsm	
First Copy Output Time	B/W ^{*7}	3.7 sec.	
	Colour ^{*8}	5.2 sec.	
Continuous Copy Speed ^{*9}	A4 LEF/ JIS B5 LEF	B/W: 55 ppm Colour: 55 ppm	B/W: 35 ppm Colour: 35 ppm
	A4 / JIS B5	B/W: 40 ppm Colour: 40 ppm	B/W: 27 ppm Colour: 27 ppm
	JIS B4	B/W: 32 ppm Colour: 32 ppm	B/W: 23 ppm Colour: 23 ppm
	A3	B/W: 27 ppm Colour: 27 ppm	B/W: 19 ppm Colour: 19 ppm
Paper Tray Capacity ^{*10}	Standard	520 sheets x 4-tray + Bypass Tray 90 sheets	
	Optional	HCF B1: 2,150 sheets	
	Max	4,320 sheets (Standard + HCF B1)	
Output Tray Capacity ^{*11}	Upper Center: 250 sheets (A4 LEF), Lower Center: 250 sheets (A4 LEF)		
Power Supply	AC220-240 V +/- 10 %, 10 A, 50/60 Hz common		
Maximum Power Consumption	2.2 kW (AC220 V +/- 10 %) 2.4 kW (AC240 V +/- 10 %) Sleep mode: 0.5 W (AC230 V) Ready mode: 111 W (AC230 V)	2.2 kW (AC220 V +/- 10 %) 2.4 kW (AC240 V +/- 10 %) Sleep mode: 0.5 W (AC230 V) Ready mode: 75 W (AC230 V)	
Dimensions	W 664 x D 723 x H 1,141 mm		
Weight ^{*12}	133 kg		

*1: Storage Device Capacity is not totally available for customers.

*2: It may change depending on usage conditions.

*3: Embedded Plug-ins / Custom Services are enabled as factory default.

*4: When using Port 9100.

*5: Up to A3 size.

*6: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

- *7: A4 LEF / Monochrome priority mode.
- *8: A4 LEF / Colour priority mode.
- *9: The speed may be reduced due to the image quality adjustment.
- *10: 80 gsm paper.
- *11: 70 gsm paper.
- *12: Excluding Toner Cartridge.

Print Function

Item		Description
Type		Built-in type
Print Size	Max	SRA3 (320 x 450 mm), 12 x 18" (305 x 457 mm), A3 [12 x 19" (305 x 483 mm), 320 x 1,200 mm ^{*1} when using Bypass Tray]
	Min	A5, Postcard (100 x 148 mm) [89 x 98 mm when using Bypass Tray]
	Image loss width ^{*2}	Lead edge 4.0 mm, Trail edge 2.0 mm, Right/Left edge 2.0 mm
Continuous Print Speed ^{*3}		Same as the Basic Specifications / Copy Function
Printing Resolution	Standard	[PCL Driver] Standard: 1,200 x 2,400 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi
	Optional	[Adobe® PostScript® 3™ Driver] High Speed (Standard): 600 x 600 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi
Page Description Language	Standard	PCL5 / PCL6
	Optional	Adobe® PostScript® 3™
Supported Operating System ^{*4}	Standard	[PCL Driver] Windows 11 (64 bit) , Windows Server 2025 (64 bit) , Windows Server 2022 (64 bit) , Windows Server 2019 (64 bit) , Windows Server 2016 (64 bit)
		[Mac OS X Driver] macOS 15 / 14 / 13 / 12
	Optional	[Adobe® PostScript® 3™ Driver] Windows 11 (64 bit) , Windows Server 2025 (64 bit) , Windows Server 2022 (64 bit) , Windows Server 2019 (64 bit) , Windows Server 2016 (64 bit)
		macOS 15 / 14 / 13 / 12
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0
	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

*1: Long paper of 106 to 220 gsm (Extra Heavyweight) is available. The printed papers are delivered to the Side Tray when C3 Finisher / C3 Finisher with Booklet Maker is attached.

*2: Up to A3 size.

*3: The speed may be reduced due to the image quality adjustment. The printing speed may be reduced depending on the document.

*4: Please refer to our official website for the latest supported OS.

Scan Function

Item		Description
Type		Colour Scanner
Scan Resolution		600 x 600 dpi, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi
Scan Speed		Same as the Scan Speed for the Duplex Automatic Document Feeder
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T
	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

Fax Function (Optional)

Item		Description
Original Size		Max: A3, 11 x 17", Long document (Longest 600 mm ^{*1})
Recording Paper Size		Max: A3, 11 x 17"; Min: A5
Transmission Time		2 seconds and more but fewer than 3 seconds ^{*2}
Transmission Mode		ITU-T G3
Applicable Lines		Public Switched Telephone Network (PSTN), PBX, Maximum 3 ports ^{*3} (G3-3 ports)

*1: When Duplex Automatic Document Feeder is used.

*2: When A4 size document with approximately 700 characters is transmitted in standard image-quality (8 x 3.85 lines/mm) and in high-speed mode (28.8 kbps or faster, JBIG). Only indicates the time for transmitting the image information and does not include the communication control time. The total communication time will vary depending on the contents of the document, the type of machine receiving the fax, and line condition.

*3: No. of FAX lines is up to 3 ports. Port refers to number of channels for FAX.

C3 Finisher / C3 Finisher with Booklet Maker (Optional)

Item		Description	
		C3 Finisher	C3 Finisher with Booklet Maker
Type	Output Tray	Sort / Stack	
	Finishing Tray	Sort (Offset available) / Stack (Offset available)	
	Booklet Tray	-	Sort / Stack
Paper Size	Output Tray	Max: 12 x 19" (305 x 483 mm), A3; Min: Postcard (100 x 148 mm)	
	Finishing Tray	Max: 12 x 19" (305 x 483 mm), A3; Min: JIS B5 LEF	
Paper Weight	Output Tray	52 to 300 gsm ^{*1}	
	Finishing Tray	52 to 300 gsm ^{*1}	
Paper Capacity ^{*2}	Output Tray	500 sheets (A4)	
	Finishing Tray	[Without Stapling] A4: 3,000 sheets, JIS B4 or larger: 1,500 sheets, Mixed Size Stacking ^{*3} : 300 sheets [With Stapling] A4: 200 sets or 3,000 sheets, JIS B4 or larger: 100 sets or 1,500 sheets Mixed Size Stacking ^{*3} : 70 sets or 200 sheets	[Without Stapling] A4: 1,500 sheets, JIS B4 or larger: 1,500 sheets, Mixed Size Stacking ^{*3} : 300 sheets [With Stapling] A4: 200 sets or 1,500 sheets, JIS B4 or larger: 100 sets or 1,500 sheets Mixed Size Stacking ^{*3} : 70 sets or 200 sheets
	Booklet Tray	-	20 sets ^{*4}
Staple	Capacity	50 sheets (90 gsm or less)	
	Paper Size ^{*5}	Max: A3, 11 x 17"; Min: JIS B5 LEF	
	Paper Weight	52 to 300 gsm	
	Position	Single stapling, Dual stapling	
Punch ^{*6}	Paper Size	A3, 11 x 17", JIS B4 ^{*7} , A4 ^{*8} , A4 LEF, Letter ^{*8} , Letter LEF, JIS B5 LEF ^{*7} , 7.25 x 10.5" (184 x 267 mm) LEF, 8 x 10" (203 x 254 mm) ^{*8} , 8 x 10" (203 x 254 mm) LEF ^{*7} , 16K (194 x 267 mm) LEF, Cover A4 (223 x 297 mm) LEF, 9 x 11" (229 x 279 mm) LEF, 215 x 315 mm ^{*8} , 8.5 x 13" (216 x 330 mm) ^{*8} , Legal ^{*8} , 11 x 15" (279 x 381 mm), 8K (267 x 388 mm)	
	Paper Weight	52 to 200 gsm	
	Number of Holes	2-hole / 4-hole punch or 2-hole / 3-hole punch (US Specifications)	
Booklet Finishing	Paper Size	-	Max: SRA3 (320 x 450 mm), 12 x 18" (305 x 457 mm), A3; Min: JIS B5
	Capacity ^{*9}	-	Saddle Staple: 16 sheets (90 gsm or less) Single Fold: 5 sheets (90 gsm or less)
	Paper Weight	-	Saddle Staple: 60 to 300 gsm Single Fold: 60 to 300 gsm
Dimensions ^{*10} / Weight ^{*11}		W 716 x D 589 x H 1,056 mm, 49 kg When Folder Unit CD1 is installed: W 953 x D 726 x H 1,056 mm, 101 kg	W 776 x D 589 x H 1,056 mm, 66 kg When Folder Unit CD1 is installed: W 1,013 x D 726 x H 1,056 mm, 118 kg

Note: Transport Unit H3 is required.

*1: 52 to 55 gsm output paper may not be aligned properly depending on the paper type.

*2: 70 gsm paper.

*3: When larger size sheets are stacked on top of smaller size sheets.

*4: When the output paper size is the same.

*5: Available staple positions vary depending on the paper size.

*6: Optional.

*7: 4-hole punch is not applicable.

*8: 3-hole punch and 4-hole punch are not applicable.

*9: The maximum number of sheets varies depending on the paper weight. Booklet may not be tightly closed depending on the size or type of the paper.

*10: When the extension tray is pulled out.

*11: Including the dedicated unit for body connection.

Folder Unit CD1 (Optional)

Item		Description
Z Fold Half Sheet	Paper Size	A3, 11 x 17", JIS B4
	Paper Weight	60 to 90 gsm
Tri-fold	Paper Size	A4 SEF, Letter SEF
	Paper Weight	60 to 90 gsm
	Paper Capacity ^{*1}	40 sheets
Power Supply ^{*2}		AC220-240 V +/- 10 %, 0.6 A, 50/60 Hz common
Maximum Power Consumption		144 W (AC220-240 V +/- 10 %)
Dimensions / Weight		W 232 x D 726 x H 992 mm, 53 kg

Note: Optional of C3 Finisher / C3 Finisher with Booklet Maker.

*1: 70 gsm paper.

*2: Power supply separate from the main unit is required.

Duplex Automatic Document Feeder B1-PC

Item	Description	
	C5570 R	C3570 R
Original Size / Paper Weight	Max: A3, 11 x 17" Min: A5 ^{*1} 38 to 128 gsm (In Duplex: 50 to 128 gsm)	
Capacity ^{*2}	130 sheets	
Scan Speed ^{*3}	Copy (A4 LEF, Simplex)	B/W: 55 ppm Colour: 55 ppm
	Scan	B/W: 35 ppm Colour: 35 ppm
		B/W: 80 ppm, Colour: 80 ppm (1 pass, 2 side scanning: B/W 154 ppm ^{*4} , Colour 154 ppm ^{*4}) [Standard Document (A4 LEF), 200 dpi, to Folder.]

*1: The minimum custom size is 125 x 85 mm.

*2: 70 gsm paper.

*3: The scanning speed varies depending on the documents.

*4: 160 ppm for both B/W and colour when Quiet Mode is disabled.

HCF B1 (Optional)

Item	Description
Paper Size	A4 LEF, Letter LEF, JIS B5 LEF
Paper Weight	55 to 216 gsm
Feeding Capacity / Number of Tray*	2,150 sheets x 1-tray
Dimensions	W 389 x D 610 x H 380 mm
Weight	29 kg

* 80 gsm paper.

Side Tray

Item	Description
Paper Capacity*	100 sheets
Dimensions	W 329 x D 567 x H 228 mm

* 70 gsm paper.

Notes

- 1) If the storage media of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall "the company" be liable for any damages whatsoever arising from loss of data.
- 2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

• This product is a remanufactured machine of Fuji Xerox product. Xerox, Xerox and Design, as well as Fuji Xerox are registered trademarks or trademarks of Xerox Corporation in Japan and/or other countries.

• Options must be purchased and installed together with remanufactured Fuji Xerox brand model. Options cannot be purchased or installed at a later date.

FUJIFILM

FUJIFILM Business Innovation Singapore Pte.Ltd.

20E Pasir Panjang Road #02-21A Mapletree Business City Singapore 117439
Tel. +65-6766-8888

fujifilm.com/fbsg

The available model varies depending on the country/region. Please ask the sales representatives for details. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. •Unused postage stamps, post cards, etc. •Certificate stamps stipulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort, Smart WelcomEyes, DocuWorks and Working Folder are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

•Microsoft, Active Directory, Azure, Microsoft Entra, Microsoft Edge, Excel, OneDrive, PowerPoint, SharePoint, Microsoft Teams, Windows, and Windows Server are registered trademarks of US Microsoft Corporation in the U.S. and other countries. •Apple, Mac, macOS, OS X, AirPrint, and AirPrint logo are trademarks of Apple Inc. registered in the U.S. and other countries and regions. •Adobe, Adobe logo, PostScript, and PostScript logo are either registered trademarks or trademarks of Adobe in the United States and/or other countries. •Mopria, the Mopria Logo, and the Mopria Alliance word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. •QR Code is a registered trademark of DENSO WAVE INCORPORATED. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.