



CAD/AEC/GIS • POS • HIGHER EDUCATION

Epson SureColor T3760D / T5760D / T7760D/DL

- Designed for high-speed, high-volume production with enhanced colour gamut
- Dual roll capability with auto loading and auto exchange
- Second roll can also be configured as an Auto Take Up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ XD3 ink for scratch and moisture resistant prints
- On-board high-speed Postscript for drag-n-drop printing
- Optional high-capacity SSD for efficient workgroup operation and rapid reprint
- Integrated pull-out media bin and optional folding flat sheet stacker
- Comprehensive warranty with on-site service up to 5 years (includes print head)¹

Epson SureColor T3760D / T5760D / T7760D/DL

Product Specifications

Print Specifications		Consumables	
Print Head	2.64" PrecisionCore™ TFP	T3760D / T5760D / T7760D	
Printing Resolution	2,400 x 1,200 dpi maximum	UltraChrome™ XD3 350 ml Ink Carts	C13T50U100~F00
Ink Type	UltraChrome XD3 aqueous pigment ink	UltraChrome™ XD3 700 ml Ink Carts	C13T50M100~F00
Colours	Photo Black, Matte Black, Cyan, Magenta, Yellow, Red	T7760DL	
Ink Sizes	350 ml / 700 ml cartridges / 1.6 L pouches ²	UltraChrome™ XD3 1.6 L Ink Pouches	C13T53A100~900
Nozzle Configuration	9600 nozzles (400 nozzles x 24 channels x 1 head)	Replacement Maintenance Box	C13S210115
Minimum Drop Size	3.5 pl	Replacement Auto Cutter Blade	C13S210117
Paper Handling		Replacement Borderless Maintenance Box	C13S210116
Loading	Single sheet and dual roll with autoloading (Second roll can optionally be configured as an Auto Take Up)	Options	
Roll Support	254 mm to 610 mm (T3760D) / 914 mm (T5760D) / 1,118 mm (T7760D/DL), 12.5 kg, 2/3" core ³ , 170 mm diam max	960GB SSD	C12C936671
Sheet Support	203 mm to 610 mm (T3760D) / 914 mm (T5760D) / 1,118 mm (T7760D/DL)	24" Flat Stacker	C12C937731
Paper Thickness	Cut-sheet: 0.07 mm to 0.8 mm Poster board: 0.8 mm to 1.5 mm Roll: 0.07 mm to 0.8 mm	36" Flat Stacker	C12C937691
Operation		44" Flat Stacker	C12C937131
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct	Additional 24" Roll Feed Spindle	C12C937711
Memory	4 GB RAM + 960 GB optional SSD	Additional 36" Roll Feed Spindle	C12C937671
Emulations	On-board High Speed Postscript, HPGL/2, HP-RTL ⁴	Additional 44" Roll Feed Spindle	C12C936171
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later	Ordering Configurations	
Product Features		T3760D Printer with 1Yr Warranty ¹	C11CH80401
Compact design with a flat top and illuminated platen All front loaded consumables Integrated pull-out media bin Optional foldable flat sheet stacker Direct front panel USB print support 4.3" colour touch screen control panel		T5760D Printer with 1Yr Warranty ¹	C11CH81401
Software Utilities		T7760D Printer with 1Yr Warranty ¹	C11CH83401
Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.		T7760DL Printer with 1Yr Warranty ¹	C11CJ74401
Environmental		T3760D Printer with 3Yr CoverPlus ¹	SCT3760D3YR
Physical	T3760D: 1,365 x 499 x 975 mm T5760D: 1,645 x 499 x 975 mm T7760D/DL: 1,848 x 499 x 975 mm	T5760D Printer with 3Yr CoverPlus ¹	SCT5760D3YR
Energy Usage	70 W Operating / 32 W Standby / 2 W Sleep	T7760D Printer with 3Yr CoverPlus ¹	SCT7760D3YR
Acoustic Noise	Approx. 50 dB/A operating	T7760DL Printer with 3Yr CoverPlus ¹	SCT7760DL3YR
		T3760D Printer with 5yr CoverPlus ¹	SCT3760D5YR
		T5760D Printer with 5yr CoverPlus ¹	SCT5760D5YR
		T7760D Printer with 5yr CoverPlus ¹	SCT7760D5YR
		T7760DL Printer with 5Yr CoverPlus ¹	SCT7760DL5YR
		What's in the box	
		Printer, 2 x roll spindles, maintenance box/es, a set of 220 ml ink cartridges for T3760D/T5760D/T7760D, and 1.6 L ink pouches for T7760DL, AC power cable, setup guide, software (some requires web download &/or registration)	

¹ Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus including the associated terms and conditions.
² 1.6 L ink pouches are for model T7760DL only.
³ 3" core for plain paper rolls only.
⁴ HP-GL/2 and HP RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP RTL language data accurately depending on your system environment or type of print data use. In order to ensure correct printing results, please make sure that you run a printing test prior to deciding on purchasing the printer. Ask your local Epson representative or Epson authorised reseller for your test.



Optional folding flat sheet stacker available for all model sizes.

Epson CoverPlus

Fast. Reliable. Professional

Better Products for a Better Future

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations. **IMPORTANT: This document contains pre-release data and specifications that are subject to change. Please refer to the websites listed below for latest information.**

V0.5 October 2021



Epson Australia Pty Ltd
Level 1, 3 Talavera Road
Macquarie Park NSW 2113
Tel: 02 8899 3666
www.epson.com.au

Epson New Zealand
Level 2, 9 Fanshawe Street
Auckland 1010
Tel: 09 366 6855
www.epson.co.nz

FUJIFILM Business Innovation New Zealand Ltd
10 - 12 Landing Drive
Mangere, Auckland 2022

FUJIFILM