

SureColor S8160

- Unparalleled productivity with dual ink slots and hot-swapping capability, allowing uninterrupted printing for high-volume production
- Outstanding image quality and colour accuracy, powered by a 6-colour ink set and a user-replaceable¹ 2.64-inch PrecisionCore MicroTFP printhead
- Integrated printhead temperature sensor for consistent, stable colour output
- Easy operation via an intuitive, tiltable 4.3-inch touchscreen panel
- Sleek, low-profile design with clear top window for easy visibility and access
- Flexible ink pack options of 800 or 1,500 ml per colour to maximise efficiency and reduce running costs
- Low-maintenance operation with automated printhead cleaning functionality
- Bundled with user-friendly Epson Edge Print Pro software
- Comprehensive service coverage, extendable up to 5 years²

SureColor S8160

Product Specifications


PRINT TECHNOLOGY	
Printhead	PrecisionCore MicroTFP
Print modes	Uni- & bi-directional
Configuration	1600 nozzles per colour
Maximum resolution	1200 x 1200 dpi
Minimum droplet size	4.3 pl
INK SYSTEM	
Ink type	Epson UltraChrome GS3
Colour set	C, M, Y, K, Lc, Lm
Ink size	800/1500 ml pouch
PRINT SPEEDS ³	
Banner	36.3 m ² /h 600 × 600 dpi 4 pass
Vinyl, Canvas and Paper	23.4 m ² /h 1200 × 600 dpi 6 pass
Film	8.9 m ² /h 1200 × 1200 dpi 16 pass
MEDIA SUPPORT	
Size	300 - 1625.6 mm wide, 250 mm max diameter
Thickness	Up to 1 mm
Weight	Up to 45 kg
OPERATION	
Control panel	4.3" touchscreen colour LCD
Interface	USB 3.0, 100Base-TX/ 1000 Base-T
Utility software	Epson Edge Print Pro, Epson Edge Dashboard, Epson Cloud Solution PORT, Web Installer, Firmware Updater, Epson Manual Launcher
OS compatibility	Windows 11, 10 (64-bit), Mac OS 10.9.5 or later
Memory	4 GB
Printer language	ESC/P Raster

PHYSICAL	
Dimensions (W x D x H)	2620 x 925 x 1021 mm
Weight	340 kg
Packaging	2980 x 1130 x 1099 mm, 520 kg
ENVIRONMENTAL	
Operational temp	15 - 35°C
Operational humidity	20 - 80%
Power supply	AC200-240V, 50/60Hz 10A
Power consumption	1350 W operating / 500 W ready / 3.4 W sleep
Operating noise	60.5 db
CONFIGURATION OPTIONS ²	
SCS81601Y	Printer with 1-yr onsite warranty
SCS81603Y	Printer with 1-yr onsite warranty + 2-yr CoverPlus
SCS81605Y	Printer with 1-yr onsite warranty + 4-yr CoverPlus
CONSUMABLES	
C13T51P192~692	800 ml ink pouch
C13T51V192~692	1500 ml Ink pouch
C13T56L092	800 ml cleaning fluid pouch
C13S210153	Maintenance parts kit
C13T724000	2 L waste ink bottle
C13S090013	Cleaning sticks
C13T699392	Ink cleaner
C13S090016	Cleaning wipes
WHAT'S IN THE BOX	
Printer, ink supply system, a set of 800 ml ink pouches, 1 x roll of GS Poster Paper, 1 x 2 L waste ink bottle, 1 x maintenance parts kit, 1 x media lifter, 1 x ink cleaner, 1 x cleaning wipes, 20 x cleaning sticks, 6 x pairs of gloves, 1 x media cleaner brush, 1 x paper tape, 1 x tweezers, 1 x metal tray, 2 x AC power cables, Epson Edge Print PRO, user manual.	


¹ To enable the user-replacement printhead feature, the printer must be registered and remain connected to Epson Cloud Solution PORT, and covered under an active CoverPlus plan. Operator is required to complete necessary training.

² CoverPlus is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for full details.

³ Figures are default print speeds only; actual production times will depend on workflow, material selection, production process, print mode, equipment settings, computing platform, file format/size and networking.



Dual 6-colour ink slots with hot-swapping



User-replaceable PrecisionCore printhead¹



4.3" tiltable touchscreen

Epson Cloud Solution
PORT

Production Tracking

Cost & Usage Analysis

Remote Monitoring

Advanced Service & Support

Epson Cloud Solution PORT

Epson CoverPlus

Fast. Reliable. Professional.

Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and are trademarks of their respective owners; Epson disclaims any and all rights. Specifications are subject to change without notice. Visit www.epson.com.au or www.epson.co.nz for the latest information.

FUJIFILM

EPSON

07/2025

FUJIFILM Business Innovation New Zealand Ltd
10 - 12 Landing Drive
Mangere, Auckland 2022