



Photo Retail • Print Service Provision

Epson SureColor P6560D (24") / P8560D/DL (44")

- Designed for high-speed, high-volume production with enhanced gradation
- Dual roll capability with auto loading and auto exchange
- Second roll can also be configured as an auto take-up
- Extremely compact design with enhanced media support and flexible networking
- Economical operation with low power consumption and cost-effective ink cartridges
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment UltraChrome™ PRO6 ink for scratch and moisture resistant prints
- On-board high-speed PostScript for drag-n-drop printing
- Optional high-capacity SSD for efficient workgroup operation and rapid reprints
- Integrated pull-out media bin and Epson Cloud Solution PORT support
- Comprehensive warranty with on-site service up to 5 years (includes print head)¹

Epson SureColor P6560D (24") / P8560D/DL (44")

Product Specifications

Print Specifications		Consumables	
Print Head	2.64" PrecisionCore™ TFP	P6560D / P8560D	
Printing Resolution	2,400 x 1,200 dpi maximum	UltraChrome™ PR06 350 ml Ink Cartridges	C13T48U100~E00
Ink Type	UltraChrome PR06 aqueous pigment ink	UltraChrome™ PR06 700 ml Ink Cartridges	C13T48M100~E00
Colours	Photo Black, Matte Black, Cyan, Magenta, Yellow, Gray	P8560DL	
Ink Sizes	350 ml / 700 ml cartridges / 1.6 L pouches ²	UltraChrome™ PR06 1.6 L Ink Pouches	C13T53F100~800
Nozzle Configuration	9600 nozzles (400 nozzles x 24 channels x 1 head)	Replacement Maintenance Box	C13S210115
Minimum Drop Size	3.5 pl	Replacement Auto Cutter Blade	C13S210117
Paper Handling		Replacement Borderless Maintenance Box	C13S210116
Loading	Single sheet and dual roll with autoloading (Second roll can optionally be configured as an auto take-up)	Options	
Roll Support	254 mm to 610 mm (P6560D) / 1,118 mm (P8560D/DL), 12.5 kg, 2/3" core ³ , 170 mm max diameter	960GB SSD	C12C936671
Sheet Support	203 mm to 610 mm (P6560D) / 1,118 mm (P8560D/DL)	Additional 24" Roll Feed Spindle	C12C937711
Paper Thickness	Cut-sheet: 0.07 mm to 0.8 mm Poster board: 0.8 mm to 1.5 mm Roll: 0.07 mm to 0.8 mm	Additional 36" Roll Feed Spindle	C12C937671
Operation		Additional 44" Roll Feed Spindle	C12C936171
Connectivity	USB 3.0, 1000/100/10 base-T network, WiFi, WiFi direct	Ordering Configurations	
Memory	RAM + 960 GB optional SSD	P6560D Printer with 1Yr Warranty ¹	C11CJ49401
Emulations	On-board High Speed Postscript, HPGL/2, HP-RTL ⁴	P6560D Printer with 3Yr CoverPlus ¹	SCP6560D3YR
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later	P6560D Printer with 5Yr Warranty ¹	SCP6560D5YR
Product Features	Compact design with a flat top and illuminated platen All front loaded consumables Integrated pull-out media bin Direct front panel USB print support 4.3" colour touch screen control panel	P8560D Printer with 1Yr Warranty ¹	C11CJ50401
Software Utilities	Printer Driver, MS Office Plug in, Epson Accounting Tool, Edge Dashboard, Print Automate, Print Layout, Device Admin, Media Installer & Epson Cloud Solution PORT support.	P8560D Printer with 3Yr CoverPlus ¹	SCP8560D3YR
Environmental		P8560D Printer with 5Yr CoverPlus ¹	SCP8560D5YR
Physical	P6560D: 1,365 x 499 x 975 mm P8560D/DL: 1,848 x 499 x 975 mm	P8560DL Printer with 1Yr Warranty ¹	C11CJ75401
Energy Usage		P8560DL Printer with 3Yr CoverPlus ¹	SCP8560DL3YR
	P8560D: 70 W Operating / 32 W Standby / 2 W Sleep	P8560DL Printer with 5Yr CoverPlus ¹	SCP8560DL5YR
	P6560D, P8560DL: 75 W Operating / 32 W Standby / 2 W Sleep	What's in the box	
Acoustic Noise	Approx. 50 dB/A operating	Printer, 2 x roll spindles, maintenance box/es, a set of 240 ml ink cartridges for P6560D/P8560D, and 1.6 L ink pouches for P8560DL, AC power cable, setup guide, software (some requires web download &/or registration)	

¹ CoverPlus on these models is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus including the associated terms and conditions.

² 1.6 L ink pouches are for model P8560DL only.

³ 3" core for plain paper rolls only.

⁴ HP-GL/2 and HP-RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP-RTL (CMYK type not supported for the latter) language data accurately depending on your system environment or type of print data use. Please ensure you run printing tests prior to purchase if these functions are essential. Contact your local Epson representative or Epson authorised reseller to arrange testing.



Epson CoverPlus

Fast. Reliable. Professional



To find out more visit www.epson.com.au/prographics/

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. All print samples shown herein are simulations.

IMPORTANT: This document contains pre-release data and specifications that are subject to change. Please refer to the websites listed below for latest information.

Epson Australia Pty Ltd
Level 1, 3 Talavera Road
Macquarie Park NSW 2113
Tel: 02 8899 3666
www.epson.com.au

Epson New Zealand
Level 2, 9 Fanshawe Street
Auckland 1010
Tel: 09 366 6855
www.epson.co.nz

VO.9 June 2023

ABN: 91 002 625 783

FUJIFILM

FUJIFILM Business Innovation New Zealand Lt

10 - 12 Landing Drive
Mangere, Auckland 2022

EPSON