



PRINT • SCAN • COPY • SHARE

Epson SureColor T5460M (36")

- Designed for CAD, GIS, POS, posters and educational applications
- Integrated large format print, scan, and copy functionality
- Prints an A1 print in as little as 22s on cut-sheet and roll media
- Economical operation with low power consumption and cost-effective ink cartridges in a choice of 350ml and 110ml capacity
- Features Epson's latest PrecisionCore® print head technology
- Uses all-pigment Ultrachrome™ XD2 ink for scratch and moisture resistant prints with super fine lines and solid fills
- High speed mono and colour scanning with support for highlighter mark-up
- Comprehensive warranty with comprehensive on-site service cover extendable up to 5 years (including the printhead)*1

Epson SureColor T5460M

Product Specifications

Print Specifications		UltraChrome™ XD2 Aqueous Pigment Inks	
Printhead	PrecisionCore™ TFP	110 ml Cartridges	
Printing Resolution	2,400 x 1,200 dpi maximum	UltraChrome™ XD2 Black	C13T41V500
Nozzle Configuration	800 nozzles per colour	UltraChrome™ XD2 Cyan	C13T41V200
Variable Drop Size	Yes, 4.0 pl minimum	UltraChrome™ XD2 Magenta	C13T41V300
Ink Type	UltraChrome XD2 aqueous pigment ink	UltraChrome™ XD2 Yellow	C13T41V400
Colours	Magenta, Yellow, Cyan, Black	350 ml Cartridges	
Ink Cartridge Sizes	110 ml/350 ml (supports mixed size cartridges)	UltraChrome™ XD2 Black	C13T41M500
Printing Speed	22 secs / A1 on plain paper	UltraChrome™ XD2 Cyan	C13T41M200
Scan Speed	19.05 cm/sec (7.5ips) mono (200dpi) ² 11.43cm/sec (4.5ips) colour (200dpi) ²	UltraChrome™ XD2 Magenta	C13T41M300
Copy Speed	44 sec colour/ 38 sec mono per A1 sheet at 200dpi ²	UltraChrome™ XD2 Yellow	C13T41M400
Paper Handling		Options	
Roll based	Single roll: 329 mm to 914 mm (36") 0.08~0.3mm thick 2/3" core, max 150/170 mm diameter	Maintenance Box	C13T699700
Sheet based	A4 to A0 0.08~0.3 mm thick	Auto Cutter Blade	C13S902007
Scan Engine	CIS with RGB filters Dual Light Source	Borderless Pad Kit	C13S400064
Scan Support	Single sheet A4 to A0, 0.8 mm max thick	Scanner Cleaning Kit	B12B819291
Connectivity	USB 3.0, 1000/100 base-T, WiFi, WiFi direct, AirPrint	A0 Document Carrier Sheet	C12C935381
Memory	1 GB RAM + 8GB Flash Memory	Roll Feed Spindle 36"	C12C933301
Emulations	HPGL/2, HP-RTL ³	Ordering Configurations	
OS Compatibility	Windows 10/8.1/8/7/Vista/XP MacOS 10.6.8 or later	T5460M with 1 Year Warranty	C11CH65401
Product Features	Direct USB printing ⁴ Scan to Tiff/Jpeg/PDF, adjustable copy scaling	T5460M with 3 Year CoverPlus	SCT5460M3YR
Software	Print Driver, LFP Print Plug-In for MS Office, LFP Account Tool, Epson Edge Dashboard	T5460M Printer with 1Yr Wty + 2 x 2Yr CoverPlus	SCT5460M5YR
Physical	1,385 x 696 x 1,060 mm (WxDxH)	What's in the box	
Energy Usage	34W operating/13W Standby/1.3W Sleep	Printer, printer stand and basket, a set of 110 ml ink cartridges, AC power cable, setup guide, software CD, maintenance box	
Acoustic Noise Level	Approx. 50 dB (operating)	<small>¹ Additional charges may apply for on-site service in non-metro areas and warranty cover may be limited if equipment is not operated and maintained appropriately. For terms and conditions on Epson Australia and New Zealand service and warranty cover please refer to the relevant web sites. ² This is the actual scan/copy time. Product specifications are subject to change without notice. ³ HP-GL/2 and HP RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP RTL language data accurately depending on your system environment or type of print data use. In order to ensure correct printing results, please make sure that you run a printing test prior to deciding on purchasing the printer. Ask your local Epson representative or Epson authorised reseller for your test. ⁴ For details please visit the relevant Epson websites For further information please contact Epson Australia Pty Limited ABN 91 002 625 783 or visit www.epson.com.au. Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.</small>	



To find out more visit www.epson.com.au/technical

The integrated high-resolution scanner supports documents up to A0 with scan to USB, scan to file, scan to email, and direct copy (with adjustable scaling).

Better Products for a Better Future

Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation. PANTONE® is the property of Pantone LLC. All other names and logos herein are for identification purpose only and are trademarks of their respective owners; Epson disclaims any and all rights. All print samples shown herein are simulations. Specifications are subject to change without notice; customers should review material posted on the web sites listed below for the latest information.

V1.0 August 2019



Epson Australia Pty Ltd
3 Talavera Road
Macquarie Park NSW 2113
Tel: 02 8899 3666
www.epson.com.au

Epson New Zealand
Level 2, 9 Fanshawe Street
Auckland 1010
Tel: 09 366 6855
www.epson.co.nz

FUJIFILM Business Innovation New Zealand Ltd

10-12 Landing Drive, Auckland Airport, Auckland 2022
Tel. 0800 493 769

fujifilm.com/fbnz