



## SureColor P7360 / P9360

- Designed for high-quality poster, photographic, proofing and fine art printing
- Innovative PrecisionCore® printhead equipped with Variable Sized Droplet Technology
- Superior print quality for consistent and predictable output in high resolution
- 10-colour ink set with violet for exceptionally vivid and rich print results
- Black Enhance Overcoat for richer blacks with better contrast and tonality
- Easy spindle-less mount operation with broad media support and tracking
- Separate Photo Black and Matte Black channels for quick and precise printing
- Large 4.3" colour LCD touchscreen for easy navigation and customisation
- Easy connection to ECS PORT with onboard Epson ES Agent
- Comprehensive onsite warranty with optional CoverPlus extension, up to 5 years\*

# SureColor P7360 / P9360

## Product Specifications

SIZE		CONFIGURATION OPTIONS*	
Max print width	P7360: 24-inch (610 mm) wide P9360: 44-inch (1,118 mm) wide	C11CL82401	SC-P7360 + 1-yr onsite warranty
<b>PRINT TECHNOLOGY</b>		SCP73603YR	SC-P7360 + CoverPlus 3-yr onsite warranty
Printhead	PrecisionCore® Micro TFP head	SCP73605YR	SC-P7360 + CoverPlus 5-yr onsite warranty
Print modes	Uni- & bi-directional	C11CL83401	SC-P9360 + 1-yr onsite warranty
Print technology	VSDT, auto head alignment, inkless nozzle checking, auto cleaning	SCP93603YR	SC-P9360 + CoverPlus 3-yr onsite warranty
Nozzle configuration	800 per colour, 10 active channels	SCP93605YR	SC-P9360 + CoverPlus 5-yr onsite warranty
Max resolution	2400 x 1200 dpi	<b>CONSUMABLES, ACCESSORIES &amp; OPTIONS*</b>	
Min droplet size	3.5 pl	C13T56U100 ~ C13T56UD00	UltraChrome PRO10 350 ml Ink Cartridges
<b>INK SYSTEM</b>		C13T56P100 ~ C13T56PD00	UltraChrome PRO10 700 ml Ink Cartridges
Ink family	UltraChrome® Pro10	C13T699700	Replacement maintenance tank
Ink type	Aqueous all-pigment	C13S210102	Borderless pad kit
Ink colours	Photo Black, Matte Black, Gray, Light Gray, Cyan, Vivid, Magenta, Yellow, Light Cyan, Vivid Light Magenta, Violet	C12C890121	Roll paper belt
Ink cartridge size	350/700 ml	C12C935931	Additional / replacement roll adaptor
<b>PERFORMANCE (A1 sheet, includes cutting time)</b>		C13S400045	Cleaning sheets
Draft	300 x 600 dpi 1.5 minutes	C13S090013	Cleaning sticks
Normal	600 x 600 dpi 2.08 minutes	C12C815331	Replacement auto cutter blade
Quality	1200 x 1200 dpi 3.22 minutes	C12C815321	Optional auto take-up unit (SC-P9360 only)
Highest Quality	2400 x 1200 dpi 6.40 minutes	C12C934551	320 GB HDD
<b>MEDIA SUPPORT</b>		YR2P7360	Yr 2 onsite Epson CoverPlus
Loading	Top spindle-less single roll / top single sheet	YR3P7360	Yr 3 onsite Epson CoverPlus
Sizing	Cut sheet: P7360 width 210 to 610 mm, P9360 width 210 to 1,118 mm Roll: P7360 width 254 to 610 mm P9360 width 254 to 1,118 mm, length 279 to 18,000 mm, diameter 150 mm	YR4P7360	Yr 4 onsite Epson CoverPlus
Thickness	0.08 - 0.5 mm roll / 0.08 - 1.5 mm sheet	YR5P7360	Yr 5 onsite Epson CoverPlus
Print margins	3 mm top & 14 mm bottom or larger. Will also print borderless on selected media sizes	YR2P9360	Yr 2 onsite Epson CoverPlus
Roll handling	Rotary auto-cutter & media barcode system	YR3P9360	Yr 3 onsite Epson CoverPlus
Output	Integrated folding bin, optional auto take-up unit (SC-P9360 only)	YR4P9360	Yr 4 onsite Epson CoverPlus
<b>OPERATION</b>		YR5P9360	Yr 5 onsite Epson CoverPlus
Control panel	4.3" LCD colour touchscreen	<b>WHAT'S IN THE BOX</b>	
Interface	High-speed USB 2.0, Ethernet 1000Base-T / 100Base-TX Printer Driver, EpsonNet Print, EpsonNet Setup Manager, Epson Print Layout, Epson Edge Dashboard, Epson Media Installer, Epson Device Admin, Device Status System (DSS), Software and Firmware Updater, Epson Cloud Solution PORT	Printer, stand, power cord, set of 110 ml inks (note 30 - 60% may be used during initialisation), 1 x spindle adaptor set, 2 x maintenance tank, output basket, installation / safety manual. The driver and utility software are available online.	
Web downloads (Windows)	Printer Driver, EpsonNet Config SE, Epson Manual Launcher, Epson Print Layout, Epson Edge Dashboard, Epson Media Installer, Firmware Updater, Epson Cloud Solution PORT	* CoverPlus is conditional on activation of Epson Cloud Solution PORT. Visit <a href="http://www.epson.com.au/coverplus">www.epson.com.au/coverplus</a> or <a href="http://www.epson.co.nz/coverplus">www.epson.co.nz/coverplus</a> for full details.	
Web downloads (Mac)	Printer Driver, EpsonNet Config SE, Epson Manual Launcher, Epson Print Layout, Epson Edge Dashboard, Epson Media Installer, Firmware Updater, Epson Cloud Solution PORT		
OS compatibility	Windows 11, 10, 8/8.1, 7, Mac OS X 10.9.5 or later		
Software compatibility	Compatible with a wide range of design, production, workflow management and RIP software		
Memory	2 GB		
<b>ENVIRONMENTAL</b>			
Operational temp	10° - 35°C (15 - 25°C recommended)		
Operational humidity	20 - 80% with no condensation (40 - 60% recommended)		
Power supply	100 - 240 V, 50 Hz - 60 Hz AC, 5 A		
Power Consumption	P7360: 70 W operating / 3.2 W sleep (1000 Base-T) P9360: 80 W operating / 3.2 W sleep (1000 Base-T)		
Operating noise	49.5 db		
<b>PHYSICAL (no ink or media)</b>			
P7360 (W x D x H)	Paper basket closed: 1401 x 667 x 1218 mm, 119 kg; Paper basket open: 1401 x 903 x 1218 mm, 119 kg; Packaging: 1497 x 802 x 1190 mm, 162 kg		
P7360 (W x D x H)	Paper basket closed: 1909 x 890 x 1218 mm, 151 kg; Paper basket open: 1909 x 1318 x 1218 mm, 151 kg; Packaging: 2050 x 827 x 1190 mm, 210 kg		



Production Tracking



Cost & Usage Analysis



Remote Monitoring



Advanced Service & Support

Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and are trademarks of their respective owners. Epson disclaims any and all rights. IMPORTANT: This document contains simplified specifications with content subject to change; for full and latest information please visit [www.epson.com.au/prographics](http://www.epson.com.au/prographics) or [www.epson.co.nz/prographics](http://www.epson.co.nz/prographics). Epson, SureColor, UltraChrome, PrecisionCore are registered trademarks of Seiko Epson Corporation.