



## Precision Meets Imagination


### Designed for premium photo printing and fine art reproduction

The Epson SureColor P5360 is the ideal choice for professional quality photographs and high-quality artwork. This series embodies the highest level of colour printing technology, boasting ultra-high resolution and an extensive colour range. It delivers exceptional results within a versatile, dependable and easily maintainable platform. Offering excellent versatility, accommodating a wide array of standard and specialized media in both roll and sheet formats

### A Superior Print



- New 10-colour UltraChrome PRO10 ink set in high-capacity 200 ml cartridges.
- Includes Violet ink for extended colour gamut in dark blue hues.
- Dedicated channels that reduce ink switching and consumption.
- Carbon Black mode for richer blacks, better contrast and tonality.
- Innovative Micro Piezo printhead equipped with Variable Sized Dot Technology (VSDT)
- Supports edge-to-edge borderless printing.



#### Supports wide range of media

Offers roll and sheet media capacity, up to 1.5mm thick. Ranging from 203mm x 254 mm to A2+ sheets.



#### Easy & Intuitive operation

Large 4.3" LCD touch screen control panel. Wi-Fi, Ethernet & USB connectivity



#### Comprehensive Warranty

1 Year manufacturer warranty with optional CoverPlus extension up to 5 years

# Product Specifications

PRINT SYSTEM	
Printhead	Epson Micro Piezo
Print Modes	Uni & bi-directional
Print Technology	Variable Sized Droplet Technology (VSDT)
Nozzle Configuration	180 per colour, 10 active channels
Max Resolution	5,760 × 1,440 dpi
Min Droplet Size	1.5 pl
Ink Family	UltraChrome® Pro10
Ink Type	Aqueous all-pigment
Ink Colours	Photo Black, Matte Black, Gray, Light Gray, Cyan, Vivid Magenta, Yellow, Light Cyan, Vivid Light Magenta, Violet
Ink cartridge size	200 ml (80 ml starter)
MEDIA SUPPORT	
Format	Roll and cut sheet
Size	203-432 mm wide x 150 mm diameter 3" core / 103 mm diameter 2" core roll, A4-A2+ sheet
Thickness	0.08-0.5 mm roll / 0.08-1.5 mm sheet
Min Margins	0 mm top, left, right & bottom roll (borderless) 3 mm top, 0 mm left & right, 3-14 mm mm bottom sheet (normal) 18 m (roll printing)
Max Print Length	18 m (roll printing)
Loading	Front and rear manual, front cassette (up to 250 plain & 100 photo sheets), top manual, top roll (spindle style with dual tension settings)
Handling	Heavy-duty rotary auto-cutter (under 5s per page) Media barcode system
Output	Front with extendable tray
OPERATION	
Control Panel	4.3" touchscreen colour LCD
Interface	High speed USB 3.0, Ethernet 10Base-T / 100Base-TX, WiFi, WiFi Direct
Web Downloads (Windows)	Printer Driver, EpsonNet Print, EpsonNet Setup Manager, Epson Print Layout, Epson Edge Dashboard, Epson ColorBase3, Epson Media Installer, Epson Device Admin, Device Status System (DSS), Epson SureLab OrderController, Software and Firmware Updater, Epson Cloud Solution PORT
Web Downloads (Mac)	Printer Driver, EpsonNet Config SE, Epson Manual Launcher, Epson Print Layout, Epson Edge Dashboard, Epson Media Installer, Epson ColorBase3iOS, Firmware Updater, Epson Cloud Solution PORT
OS Compatibility	Windows 11, 10, 8/8.1, 7 Mac OS X 10.9.5 or later
Software Compatibility	Compatible with a wide range of design, production, workflow management and RIP software (see website for details)
Memory	1 GB
Language	ESC/P Raster

ENVIRONMENTAL	
Operational Temperature	10° to 35° C (15-25° C recommended)
Operational Humidity	20 to 80% with no condensation (40-60% recommended)
Power Supply	100 - 240 V, 50 Hz - 60 Hz AC, 2A
Power Consumption	42 W Operating / 17 W Standby / 2.4 W Sleep
Operating Noise	46 dB
PHYSICAL	
Dimensions (WxHxD)	Paper basket closed: 863 mm x 766 mm x 405 mm Paper basket open: 863 mm x 1134 mm x 405 mm
Weight	53 kg (no ink or media)
Packaging	1032 mm x 593 mm x 912 mm
CONSUMABLES	
C13T55W100	200 ml Photo Black Ink Cartridge
C13T55W200	200 ml Cyan Ink Cartridge
C13T55W300	200 ml Vivid Magenta Ink Cartridge
C13T55W400	200 ml Yellow Ink Cartridge
C13T55W500	200 ml Light Cyan Ink Cartridge
C13T55W600	200 ml Vivid Light Magenta Ink Cartridge
C13T55W700	200 ml Gray Ink Cartridge
C13T55W800	200 ml Matte Black Ink Cartridge
C13T55W900	200 ml Light Gray Ink Cartridge
C13T55WD00	200 ml Violet Ink Cartridge
CONFIGURATION OPTIONS <sup>1</sup>	
C11CL14402	P5360 Printer with 1Yr Warranty <sup>1</sup>
SCP53603YR	P5360 Printer with 3Yr Warranty <sup>1</sup>
SCP53605YR	P5360 Printer with 5Yr Warranty <sup>1</sup>
ACCESSORIES & OPTIONS	
C12C890121	Roll Paper Belt
C12C815351	Replacement Auto Cutter Blade
C13T619100	Replacement Borderless Maintenance Tank
C13T619000	Replacement Maintenance Tank
C12C811251	Additional Dual Tension Roll-Feed Spindle
C13S400045	Cleaning Sheet
COVERPLUS <sup>1</sup>	
YR2P5360	Yr 2 On-Site Epson CoverPlus
YR3P5360	Yr 3 On-Site Epson CoverPlus
YR4P5360	Yr 4 On-Site Epson CoverPlus
YR5P5360	Yr 5 On-Site Epson CoverPlus
WHAT'S IN THE BOX	
	Printer, power cord, set of 80 ml inks (20-50% of each loaded cart will be used to charge the machine during initialisation), 1 x maintenance tank, 1 x borderless maintenance tank, 1 x borderless printing spacer, installation/safety manual

<sup>1</sup> CoverPlus on these models is conditional on activation of Epson Cloud Solution PORT. Please refer to the Epson Australia or New Zealand website for details on warranty and CoverPlus, including the associated terms and conditions.



Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and are trademarks of their respective owners. Epson disclaims any and all rights. **IMPORTANT: This document contains simplified specifications with content subject to change; for full and latest information please see the relevant Epson website.**

Epson Australia Pty Ltd  
Level 1, 3 Talavera Road

www.epson.com.au

Epson New Zealand  
Level 2, 9 Fanshawe Street  
Auckland 1010  
Tel: 09 366 6855  
www.epson.co.nz

V2.0 Dec 2023

**FUJIFILM**

FUJIFILM Business Innovation New Zealand Ltd  
10 - 12 Landing Drive  
Mangere, Auckland 2022

**EPSON**