



SPEAK 750 for Unified Communications

Engineered to power your meetings with seamless, premium audio

Hear and be heard when it matters

Jabra Speak 750 comes with full duplex audio, allowing you to hold completely natural conversations via speakerphone. With full duplex audio, both sides of the conversation are transmitted at the same time, allowing your conversations to flow just as they do in person. So, you can get on with what's important, without worrying about whether you're being heard.

Works with all leading UC platforms

Versatile and easy to use, and compatible with all leading Unified Communications platforms. Certified for use with UC, for an accessible, seamless connection experience, and maximum flexibility when connecting with colleagues around the world. Enjoy a seamless meeting experience, whatever platform you're using.

Plug-and-play for instant collaboration

Connect instantly with plug-and-play capability. With 10% of the average meeting being wasted on technical difficulties, simply being able to plug-and-play to your laptop, smartphone or tablet, using either USB or Bluetooth®, makes collaboration so much easier. Meetings are much more effective when your technology works first time.

Connects to:



HOW TO CONNECT

to PC or softphone using Jabra Link 370 USB Bluetooth Adapter



Plug the Link 370 Bluetooth Adapter into a USB port on your PC. Speak 750 and Link 370 are already pre-connected.


HOW TO PAIR

with Bluetooth enabled devices

- 1. Tap power to switch on
- 2. Hold (2 sec) the Bluetooth button
- 3. Follow the voice instructions to pair to your device or laptop



HOW TO USE



	FEATURES	BENEFITS
Connectivity	USB cable	Plug-and-play connectivity to PC Softphone/UC systems
	Bluetooth	Easy Bluetooth connectivity to smartphones and tablets
	Jabra Link 370 USB Bluetooth Adapter (Unified Communications version)	Wireless range of up to 100 feet/30 meters
Audio	Full compatibility with UC systems & VoIP clients	Seamless integration and call control with leading UC systems/PC softphones.
	High performing Omnidirectional microphone	A 360° sound pick-up allowing attendees to be heard from all angles
	HiFi grade speaker	Ideal for outstanding voice, music and multimedia experience with more speaker power and output
	Digital Signal Processing (DSP) technology	Crystal clear sound without echoes or distorted sounds even at maximum volume level
	Wideband audio/HD Voice	High quality audio for best possible voice collaboration
Ease of use	Talk time	Up to 11 hours battery life
	LED indicators	Intuitive user interface
	Folding stand	Fold out the stand to be upright for optimized music experience or fold it down flat to the table, for enhanced group conference calls and collaboration
	Link button	One touch button to pair two Speak 750 devices together for full stereo and true immersive sound for calls and music
	Smart button	Integrate your smartphone digital assistant using MS Cortana, Siri® or Google Assistant™, or customize your Speak 750 for speed dial using Jabra Direct software
Accessories	Jabra Link 370, USB Bluetooth Adapter (Unified Communications version)	Easy Bluetooth connection to your PC
	Kensington Lock Adapter	Optimized theft protection
	Jabra Speak 710/750 Secure Mount	Secure to tables
	Jabra Soft Travel Pouch	Travel pouch included to protect your speakerphone on the go