



DESIGNED FOR ENDLESS POSSIBILITIES.



SC-T3130/T3130N



SC-T3130X*



SC-T5130

Distinctive Quality Meets Endless Possibilities For Your Creative Ideas.



Take your ideas to a bigger scale with greater performance and precision with the Epson SureColor T-series printers. With PrecisionCore printheads, and UltraChrome XD2 ink to bring fast printing speeds, seamless work process and top-class accuracy in every print. Showcase your ideas and plans in a big way right down the finest detail.


GO BIG on the details and find out more from our printing experts.

*SC-T3130X stand is optional and is not included in the initial packaging.

IT'S IN THE DETAILS.

EPSON
EXCEED YOUR VISION

For accuracy right down to the finest details, the Epson SureColor T-series printers fulfil all your business needs. Using core technologies such as PrecisionCore printheads and UltraChrome XD2 ink, prints are delivered at an outstanding speed with impressive accuracy and clarity. Let your ideas impress your audience with prints that are consistently fast, precise and reliable.



Compact, User-Friendly Design

Small Footprint

Sleek and minimally designed, the T-series is of a comfortable size that fits into tight work spaces effortlessly. At just 970 x 245 x 577mm without the stand, the SC-T3130X has one of the smallest footprint in its class.



Ideal For Corners

As the printers are built for a full front operation, it can be placed ideally in any corner of the office, without taking up too much space.



User Convenience In Mind

Designed with the user in mind, the printer will print and cut printouts without dropping it from the printer, until it is ready to be collected.



Ergonomically Design

Designed with the user in mind, the T-series printers' smart design can cater to users of different heights to help make it comfortable for them to load the media as well as to operate the printers.



Trusted Productivity

Continuous Ink Supply System (CISS)*

The SC-T3130X is fitted with a Continuous Ink Supply System (CISS) for a seamless workflow without the need for ink replacements to delay print jobs. With an efficiently designed ink tank and system, ink refills during print jobs can be easily and effortlessly done, without compromising on efficiency.

*Applicable for SC-T3130X



Wireless Connectivity

The T-series is integrated with Wi-Fi and Wi-Fi Direct, making it convenient to print right from smart devices from anywhere in the office. The Wi-Fi Direct function acts as an access point, allowing devices to connect directly to the printer without a router. Additionally, the T-series printers come equipped to allow direct wireless printing from any Apple devices through Apple AirPrint*, without the need for any additional drivers.

*Apple AirPrint is a trademark of Apple Inc.



LARGE FORMAT PRINTERS

SURECOLOR™ SC-T3130/T3130N/T3130X/T5130


Control At Your Fingertips

A 4.3 inch touch panel on the T-series gives you the convenience of an easy setup and a PC-less operation that just makes things extra efficient.



Preview Before Printing

Save time and money when you preview your documents before printing, preventing accidental misprints that could otherwise lead to wastage.




Seamless Scan To Print

Scan and enlarge your printouts in just four easy steps without needing to connect to a computer.


Using compatible Epson scanners* for the SC-T3130/T3130N/T3130X/T5130, you can seamlessly scan and print directly from the T-series printers.

*Recommended scanners: WorkForce DS-530, DS-6500, DS-60000.



Precision Printhead Technology


The T-series comes equipped with the next-generation PrecisionCore printhead technology, enabling superior print speed, quality and reliability. PrecisionCore technology utilises piezo elements to mechanically eject the ink. This heatless technology prolongs printhead longevity, providing reliable long-term operation.



The PrecisionCore technology, as well as Variable Size Dot Technology, allow the ink droplets to be controlled to the finesse of 3.5 picolitres.

Nozzle Verification Technology

Print without interruptions with the advanced built-in Nozzle Verification Technology (NVT). This technology monitors nozzle health and adjusts print quality automatically without interruption, even during printing.



The piezo element (sensor) detects the residual vibration (pressure change) in the ink chamber and diagnoses the nozzle condition.

If a clogged nozzle is indicated by an irregular vibration pattern, the printer automatically adjusts the print quality.



Anti-dust Design

Incorporating a unique anti-dust design, the T-Series printers require minimal cleaning and maintenance that are required for environments that are traditionally dusty, such as, construction sites.



Outstanding Speed & Quality



Impressive Print Speeds

The PrecisionCore printhead technology enables remarkable print speeds that will print A1 printouts in 31 seconds*.

*Print speed is based on the SC-T5130.

Advanced Printhead

The next generation of inkjet comes in the form of the PrecisionCore Micro TFP printhead, delivering Epson's renowned, industry leading output quality, reliability and accuracy. The Epson SureColor T-series produces extremely precise line detail, crisp text and true photographic-quality graphics — all at outstanding print speeds.

Applications

Engineering

Print incredible detail, fast


Low costs and high speeds make the T-series printers ideal for engineers. Produce detailed and accurate large-scale drawings, renderings, schematics, blueprints, and more whenever you need to. Long performance printheads and less frequent cartridge recharging means you control the quality of the prints saving you time and boosting your profits.



Construction

Control costs and increase flexibility

Impress your clients and partners with your presentation of large format documents and plans with superb image clarity, quality and detail. Rapidly and accurately create indoor building signage, building wraps, scaffolding covers and large mesh banners in-house and cost-effectively. With a technical printer, putting the CAD drawings or other plan renderings on paper is easy.



LARGE FORMAT PRINTERS

SURECOLOR™ SC-T3130/T3130N/T3130X/T5130

Architects

Display your CAD designs in outstanding detail

Create new perspectives and allow your clients and associates to explore the richness of your designs, renderings and graphs with stunning full-colour displays, brilliant detail and sharp photography. The T-Series technical printers handles the requirements of CAD printing and plotting, blueprints, along with the business proposals and documents that are needed for the client and legal aspects of your projects.



Advertising Agencies

Get noticed and get your message across

Make a splash and grab your clients' attention by creating vibrant, customer eye-catching advertisements quickly and seamlessly. Print everything from large photo quality posters to banners. The T-series printers will increase your marketing efficiency, allowing you to transition from one marketing creation to the next with ease.



Small Businesses

Embrace your creativity

From posters to banners to presentations to graphics, what says more about your business than big, bold images of customers enjoying your products or services? The T-series printers elevate your brand's image to a level beyond anything you could imagine, making your business stand out from the crowd and really shine.



Education

Inspire young minds

Schools, colleges and universities are often required to have the latest technology to encourage and inspire the next generation. Enthuse students and teachers alike by generating stunning printed collateral for the classroom and print promotional materials for school events, in-house.



LARGE FORMAT PRINTERS
SURECOLOR™ SC-T3130/T3130N/T3130X/T5130



MODEL NUMBER	SC-T3130 SC-T3130N	
Printer Width	24"	
Printing Technology		
Technology 1	PrecisionCore Inkjet Technology	
Technology 2	Variable-Sized Droplet Technology	
Printhead	PrecisionCore TFP Printhead	
Nozzle Configuration	3200 nozzles (800 nozzles x 4 channels x 1 head)	
Maximum Resolution	2400 x 1200 dpi	
Minimum Ink Droplet Volume	4.0pl	
Print Speed	CAD A1: 34 sec	
Ink System		
Ink Type	UltraChrome XD2 Pigment Ink	
Colours	Cyan, Magenta, Yellow, Black	
Ink Capacity	CMY: 26ml/50ml, K: 50ml/80ml	
Ink Case	Ink Cartridge	
Paper Handling		
Paper Path	Friction Feed	
Maximum Roll Diameter / Weight	2" core, Max. 110 mm/3kg	
Paper Width (Roll)	Roll: 329mm - 610mm Cutsheet(ASF): A4 to A3 Cutsheet: 210 mm - 610 mm	
Paper Thickness	Roll: 0.05 mm to 0.21 mm ASF/Cutsheet: 0.12 mm to 0.27 mm 4.3 inch touch screen	
Control Panel		
Connectivity		
Printer Interfaces	Super-Speed USB*, 100BASE-TX / 1000BASE-T/IEEE802.11b/g/n	
Printer Languages	ESC/P rasterHP-GL/2HP RTL	
Memory	1GB	
Power and Operating Requirements		
Power Requirements	AC 100 to 240V ; Frequency: 50/60Hz	
Rated Current	1.4A	
Power Consumptions	Operating: Approx. 28W Ready: Approx. 8W Sleep: Approx. 1.6W Power Off (Stand by): Approx. 0.2W	
Temperature	Operating: 10°C to 35°C, Storage: -20°C to 40°C	
Humidity	Operating: 20 - 80% (no condensation), Storage: 5 - 85% (no condensation)	
Acoustic Noise Level		
Sound Pressure Level <db(A)>	Operating: Approx. 49.5dB(A), Sleep: Approx. 32dB(A)	
Sound Power Level <B(A)>	Operating: Approx. 7.5B(A)	
Utility Software		
Utility Software (Bundled in CD)	Windows Install Navi - Printer driver - EpsonNet Setup - EpsonNet Print - EpsonNet Config - Epson Software Updater - LFP Print Plug-in for Office - Epson Manuals - Mac Setup Navi	
Utility Software (Web delivery)	Windows Install Navi - Firmware Updater - HDI Driver - CopyFactory - EpsonNet Setup Manager - Mac Install Navi - Printer driver - EpsonNet Config - Epson Software Updater - Uninstaller - Epson Manuals - Firmware Updater Linux Printer driver	
Printer Dimensions		
Storage Dimensions (W x H x D)	970mm x 913mm x 696mm	970mm x 230mm x 505mm
Printing Dimensions (W x H x D)	970mm x 913mm x 982mm	970mm x 230mm x 982mm
Weight	38kg	27kg
What's in the box	Printer, Printer stand*, Initial ink cartridge, AC power cable, Setup guide, Software CD-ROM, Maintenance box	
Options	Roll Feed Spinder (24")	
Consumables	Auto Cutter Spare Blade, Maintenance Box, Ink	
Warranty	3 years	

*SC-T3130N does not come with printer stand

SC-T3130
Dimension & Weight
Weight: 38kg



SC-T3130N
Dimension & Weight
Weight: 27kg



LARGE FORMAT PRINTERS
SURECOLOR™ SC-T3130/T3130N/T3130X/T5130



MODEL NUMBER	SC-T3130X		SC-T5130
Printer Width	24"		36"
Printing Technology			
Technology 1	PrecisionCore Inkjet Technology		
Technology 2	Variable-Sized Droplet Technology		
Printhead	PrecisionCore TFP Printhead		
Nozzle Configuration	3200 nozzles (800 nozzles x 4 channels x 1 head)		
Maximum Resolution	2400 x 1200 dpi		
Minimum Ink Droplet Volume	3.8pl		4.0pl
Print Speed	34 seconds		31 seconds
Ink System			
Ink Type	Black: Pigment Ink, Colour: Dye Ink		UltraChrome XD2 Pigment Ink
Colours	Cyan, Magenta, Yellow, Black		
Ink Capacity	140ml		CMY: 26ml/50ml, K: 50ml/80ml
Ink Case	Ink Bottle		Ink Cartridge
Paper Handling			
Paper Path	Friction Feed		
Maximum Roll Diameter/Weight	2" core, Max. 110 mm/3kg		2" core, Max. 110 mm/5kg
Paper Width (Roll)	Roll: 329 mm to 610 mm		Roll: 329mm to 914 mm
	Cutsheet (ASF): A4 to A3		Cutsheet (ASF): A4 to A3
	Cutsheet: 210 mm to 610 mm		Cutsheet (1 sheet): 210 mm to 910 mm
Paper Thickness	Roll: 0.05 mm to 0.21 mm		
	ASF/Cutsheet: 0.12 mm to 0.27 mm		
	4.3 inch touch screen		
Control Panel			
Connectivity			
Printer Interfaces	Super-Speed USB*, 100BASE-TX/1000BASE-T/IEEE802.11b/g/n		
Printer Languages	ESC/P raster HP-GL/2HP RTL		
Memory	1GB		
Power and Operating Requirements			
Power Requirements	AC 100 to 240V ; Frequency: 50/60Hz		
Rated Current	1.4A		
Power Consumptions	Operating: Approx. 22W		Operating: Approx. 28W
	Ready: Approx. 8W		Ready: Approx. 8W
	Sleep: Approx. 1.6W		Sleep: Approx. 1.6W
	Power Off (Stand by): Approx. 0.2W		Power Off (Stand by): Approx. 0.2W
	Operating: 10°C to 35°C, Storage: -20°C to 40°C		
Temperature	Operating: 20 - 80% (no condensation), Storage: 5 - 85% (no condensation)		
Humidity			
Acoustic Noise Level			
Sound Pressure Level <db(A)>	Operating: Approx. 50dB(A), Sleep: Approx. 32dB(A)		Operating: Approx. 49.5dB(A), Sleep: Approx. 32dB(A)
Sound Power Level <B(A)>	Operating: Approx. 7.5B(A)		Operating: Approx. 7.5B(A)
Utility Software			
Utility Software (Bundled in CD)	Windows Install Navi - Printer driver - EpsonNet Setup - EpsonNet Print - EpsonNet Config SE - Epson Software Updater - Epson Manuals - Manual Luncher - Epson Control Dashboard Mac Setup Navi EpsonNet Config SE Epson Software Updater		Windows Install Navi - Printer driver - EpsonNet Setup - EpsonNet Print - EpsonNet Config - Epson Software Updater - LFP Print Plug-in for Office - Epson Manuals Mac Setup Navi
Utility Software (Web delivery)	Windows Install Navi - Web Installer - Firmware Updater - PS Driver - HDI Driver XPS Driver - EpsonNet Setup Manager - Epson Device Admin - Epson Edge Dashboard - Epson Edge Print - Epson Print Layout - LFP Accounting tool - Adobe ICC Profiles - Mac Web Installer - Install Navi - Printer driver - EpsonNet Config - Epson Software Updater - Uninstaller - Epson Manuals - Firmware Updater Linux Printer driver		Windows Install NaviFirmware Updater - HDI Driver CopyFactory - EpsonNet Setup Manager Mac Install Navi - Printer driver - EpsonNet Config - Epson Software Updater - Uninstaller - Epson Manuals - Firmware Updater Linux Printer driver
Printer Dimensions			
Dimension w/o Stand (W x H x D)	970mm x 245mm x 577mm		1268mm x 913mm x 696mm
Dimension with Stand (W x H x D)	970mm x 245mm x 811mm		1268mm x 913mm x 811mm
Weight	29kg		46kg**
What's in the box	Printer, Initial ink, AC power cable, Setup guide, Software CD-ROM, Maintenance box		Printer, Printer stand, Initial ink cartridge, AC power cable, Setup guide, Software CD-ROM, Maintenance box,
Options	Stand (24"), Roll Feed Spindle (24")		Roll Feed Spindle (36")
Consumables	Ink, Replacement Printer Cutter Blade, Replacement Ink Maintenance Tank		Ink, Auto Cutter Spare Blade, Maintenance Box
Warranty	1 year warranty		3 years warranty

*Compatible with the USB 3.0 Specification.
**Approx. with stand

SC-T3130X
Dimension & Weight
Weight: 29kg



SC-T5130
Dimension & Weight
Weight: 46kg



© 2020 Epson Singapore Pte Ltd. All Rights Reserved.
Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited. EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation. All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. Print samples shown are simulations only. Specifications and product availability are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

FUJIFILM
For more information or detailed product specification, please call or visit us at
FUJIFILM Business Innovation Philippines Corp.
25th Floor SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines
Tel. 632-8878-5200
fujifilm.com/tbph

Information correct at time of printing
Printed February 2020