

ApeosPort® 3410SD

A4 Monochrome Multifunction Printer

Features



B/W



34 ppm



Copy

Print

Fax

Scan



High Performance & Productivity

- Compact design sits comfortably onto your desktop or small work space
- Fast monochrome printing of up to 34 ppm
- Equipped with an Automatic Document Feeder that supports scanning up to 23 ppm for Monochrome, 7 ppm for Colour, and a 250-sheet tray as standard equipment
- Easy to connect with built-in Wi-Fi, Ethernet or USB

Security

- Prevents information leakage with Confidential Print function
- Controls access to the MFPs functions
- Supports settings to delete temporary data files in memory

Easy Operation

- Two-line LCD lets you configure and monitor vital system information
- Supports ID Copy function, which allows you to Copy the front and back of an ID card onto one side of a single sheet
- Compatible with Mopria® and AirPrint, you can easily print from mobile devices

Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner

2-line Monochrome
LCD Panel

Automatic Document
Feeder

Output tray
(150-Sheet)

Manual feeder
(1-Sheet)

Standard tray
(250-Sheet)



Specifications

Printing	
Display	2-line All Points Addressable (APA) monochrome LCD display
Print Speed: Up to	Black: 34 ppm (A4)
Time to First Page: As fast as ^{*1}	Black: 8 seconds
Print Resolution	Black: 1200 Image Quality, 2400 Image Quality, 300 x 300 dpi, 600 x 600 dpi
Memory	512 MB
Hard Disk	Not Available
Copying	
Copy Speed: Up to	Black: 34 ppm (A4)
Time to First Copy: As fast as ^{*2}	Black: 8.0 seconds
Scanning	
Scanner Type / ADF Scan	Flatbed scanner with ADF / Simplex
A4/Ltr Simplex Scan Speed: Up to	Black: 23 / 25 ppm / Colour: 7 / 8 ppm
ADF Paper Input Capacity: Up to	50 pages 75 gsm
Faxing	
Modem Speed	Max is 33,600 bps, V.34 Half-Duplex Kbps
Supplies	
Toner Cartridge Yields (up to)	3,000-page High Yield Cartridge, 6,000-page Extra High Yield Cartridge
Imaging Unit Estimated Yield: Up to	12000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	700-page Toner Cartridges
Paper Handling	
Included Paper Handling	250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed
Paper Input Capacity: Up to	251 pages 75 gsm
Paper Output Capacity: Up to	150 pages 75 gsm
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope, Hagaki
General Information	
Standard Ports	Ethernet 10/100BaseTX (RJ-45), USB 2.0 Specification Hi-Speed Certified (Type B), 802.11b/g/n Wireless ^{*3}
Noise Level: Operating	Print: 52 dBA / Copy: 55 dBA / Scan: 52 dBA
Specified Operating Environment ^{*4}	Humidity: 15 to 80% ^{*5} Relative Humidity, Temperature: 10 to 32°C ^{*6} (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	352 x 415 x 360 mm / 11.4 kg

^{*1}: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. ^{*2}: Numeric value varies depending on the output environment. ^{*3}: This description is for SGP IMDA : Rated RF output power <20 dBm EIRP, Frequency range 2412 – 2472 MHz. ^{*4}: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. ^{*5}: When the humidity is 80%, the temperature is 25.5°C or less. ^{*6}: Humidity 45% or less when the temperature is 32°C.

Consumables^{*1}

Product Name	Product Code	Product Life
Black High Yield Use and Return Toner Cartridge ^{*2}	CT203483	Up to 3,000 pages
Black Extra High Yield Use and Return Toner Cartridge ^{*2}	CT203482	Up to 6,000 pages
Black Extra High Yield Regular Toner Cartridge	CT203528	Up to 6,000 pages
Black Imaging Unit	CT351281	Up to 12,000 pages

^{*1}: Average standard page yield value declared in accordance with ISO/IEC 19752.

^{*2}: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

FUJIFILM Business Innovation Singapore Pte. Ltd.

fujifilm.com/fbsg

20E Pasir Panjang Road #02-21A Mapletree Business City Singapore 117439 Tel.+65-6766-8888

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

•Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April,2023

PIC-0197 SG (2111-R1)